


## 20 A - 600 V H-series Snubberless Triac



### Features

- Medium current Triac
- 150 °C max.  $T_j$  turn-off commutation
- Low thermal resistance with clip bonding
- Very high 3 quadrant commutation capabilities
- Packages are RoHS (2002/95/EC) compliant
- UL certified (ref. file E81734)

### Applications

Especially designed to operate in high power density or universal motor applications such as vacuum cleaner and washing machine drum motor.

### Description

Available in through-hole or surface mount packages, these Triac series are suitable for general purpose mains power ac switching.

These 20 A Triacs provide a very high switching capability up to junction temperatures of 150 °C.

The heatsink can be reduced, compared to traditional Triacs, according to the high performance at given junction temperatures.

By using an internal ceramic pad, they provide voltage insulation (rated at 2500  $V_{RMS}$ ).

The surface mount D<sup>2</sup>PAK package enables compact SMD based designs for automated manufacturing.

#### Product status link

[T2035H-6I, T2035H-6T, T2035H-6G,  
T2050H-6I, T2050H-6T, T2050H-6G](#)

#### Product summary

|                   |             |
|-------------------|-------------|
| $I_{T(RMS)}$      | 20 A        |
| $V_{DRM}/V_{RRM}$ | 600 V       |
| $I_{GT}$          | 35 or 50 mA |

# 1 Characteristics

**Table 1. Absolute maximum ratings (limiting values)**

| Symbol            | Parameter                                                                                       |                                 |                       | Value                   | Unit             |
|-------------------|-------------------------------------------------------------------------------------------------|---------------------------------|-----------------------|-------------------------|------------------|
| $I_{T(RMS)}$      | RMS on-state current (full sine wave)                                                           | D <sup>2</sup> PAK,<br>TO-220AB | $T_c = 128\text{ °C}$ | 20                      | A                |
|                   |                                                                                                 | TO-220AB Ins.                   | $T_c = 108\text{ °C}$ |                         |                  |
| $I_{TSM}$         | Non repetitive surge peak on-state current (full cycle,<br>$T_j$ initial = 25 °C)               | f = 50 Hz                       | t = 20 ms             | 200                     | A                |
|                   |                                                                                                 | f = 60 Hz                       | t = 16.7 ms           | 210                     |                  |
| $I^2t$            | $I^2t$ value for fusing                                                                         |                                 | $t_p = 10\text{ ms}$  | 265                     | A <sup>2</sup> s |
| di/dt             | Critical rate of rise of on-state current, $I_G = 2 \times I_{GT}$ , tr<br>≤ 100 ns, f = 100 Hz | f = 120 Hz                      | $T_j = 25\text{ °C}$  | 100                     | A/μs             |
| $V_{DSM}/V_{RSM}$ | Non Repetitive peak off-state voltage                                                           | $t_p = 10\text{ ms}$            | $T_j = 25\text{ °C}$  | $V_{DRM}/V_{RRM} + 100$ | V                |
| $I_{GM}$          | Peak gate current                                                                               | $t_p = 20\text{ μs}$            | $T_j = 150\text{ °C}$ | 4                       | A                |
| $P_{G(AV)}$       | Average gate power dissipation                                                                  |                                 | $T_j = 150\text{ °C}$ | 1                       | W                |
| $T_{stg}$         | Storage temperature range                                                                       |                                 |                       | -40 to +150             | °C               |
| $T_j$             | Operating junction temperature range                                                            |                                 |                       | -40 to +150             | °C               |

**Table 2. Electrical characteristics ( $T_j = 25\text{ °C}$ , unless otherwise specified)**

| Symbol                              | Test conditions                           | Quadrants             |      | Value  |        | Unit |
|-------------------------------------|-------------------------------------------|-----------------------|------|--------|--------|------|
|                                     |                                           |                       |      | T2035H | T2050H |      |
| $I_{GT}^{(1)}$                      | $V_D = 12\text{ V}$ , $R_L = 33\text{ Ω}$ | I - II - III          | Max. | 35     | 50     | mA   |
| $V_{GT}$                            |                                           |                       | Max. | 1.0    |        | V    |
| $V_{GD}$                            | $V_D = V_{DRM}$ , $R_L = 3.3\text{ kΩ}$   | I - II - III          | Max. | 0.15   |        | V    |
| $I_L$                               | $I_G = 1.2 \times I_{GT}$                 | I - III               | Max. | 50     | 90     | mA   |
|                                     |                                           | II                    | Max. | 80     | 110    |      |
| $I_H^{(2)}$                         | $I_T = 500\text{ mA}$ , gate open         |                       | Max. | 35     | 75     | mA   |
| dV/dt <sup>(2)</sup>                | $V_D = 2/3 \times V_{DRM}$ , gate open    | $T_j = 150\text{ °C}$ | Min. | 1000   | 1500   | V/μs |
| (di/dt) <sub>c</sub> <sup>(2)</sup> | Without snubber                           | $T_j = 150\text{ °C}$ | Min. | 27     | 36     | A/ms |

1. Minimum  $I_{GT}$  is guaranteed at 20% of  $I_{GT}$  max.

2. For both polarities of A2 referenced to A1.

**Table 3. Static characteristics**

| Symbol            | Test conditions                                         |                                    |      | Value | Unit          |
|-------------------|---------------------------------------------------------|------------------------------------|------|-------|---------------|
| $V_T^{(1)}$       | $I_T = 28 \text{ A}$ , $t_p = 380 \text{ } \mu\text{s}$ | $T_j = 25 \text{ }^\circ\text{C}$  | Max. | 1.5   | V             |
| $V_{TO}^{(1)}$    | Threshold voltage                                       | $T_j = 150 \text{ }^\circ\text{C}$ | Max. | 0.80  | V             |
| $R_D^{(1)}$       | Dynamic resistance                                      | $T_j = 150 \text{ }^\circ\text{C}$ | Max. | 19    | m $\Omega$    |
| $I_{DRM}/I_{RRM}$ | $V_D = V_R = 600 \text{ V}$                             | $T_j = 25 \text{ }^\circ\text{C}$  | Max. | 5     | $\mu\text{A}$ |
|                   |                                                         | $T_j = 150 \text{ }^\circ\text{C}$ |      | 6.2   | mA            |
|                   | $V_D = V_R = 400 \text{ V}$ , peak voltage              | $T_j = 150 \text{ }^\circ\text{C}$ | Max. | 5.0   | mA            |
|                   | $V_D = V_R = 200 \text{ V}$ , peak voltage              | $T_j = 150 \text{ }^\circ\text{C}$ | Max. | 4.0   |               |

1. For both polarities of A2 referenced to A1.


2.  $t_p = 380 \text{ } \mu\text{s}$

**Table 4. Thermal resistance**


| Symbol        | Parameter                                         |                                 | Value | Unit               |
|---------------|---------------------------------------------------|---------------------------------|-------|--------------------|
| $R_{th(j-c)}$ | Junction to case (AC)                             | D <sup>2</sup> PAK,<br>TO-220AB | 1.0   | $^\circ\text{C/W}$ |
|               |                                                   | TO-220AB Ins.                   | 1.9   |                    |
| $R_{th(j-a)}$ | Junction to ambient ( $S_{cu} = 2 \text{ cm}^2$ ) | D <sup>2</sup> PAK,<br>TO-220AB | 45    | $^\circ\text{C/W}$ |
|               | Junction to ambient                               | TO-220AB Ins.                   | 60    |                    |

## 1.1 Characteristics (curves)


**Figure 1. Maximum power dissipation versus on-state RMS current**




**Figure 2. On-state RMS current versus case temperature**












**Figure 3. On-state RMS current versus ambient temperature**



**Figure 4. Variation of thermal impedance versus pulse duration**



**Figure 5. On-state characteristics (maximum values)**

**Figure 6. Surge peak on-state current versus number of cycles**

**Figure 7. Non-repetitive surge peak on-state current for a sinusoidal pulse**

**Figure 8. Relative variation of  $I_{GT}$ ,  $I_H$ ,  $I_L$  vs junction temperature (typical values)**

**Figure 9. Relative variation of critical rate of decrease of main current  $(dI/dt)_c$  versus reapplied  $(dV/dt)_c$** 

**Figure 10. Relative variation of critical rate of decrease of main current versus junction temperature**



**Figure 11. Leakage current versus junction temperature for different values of blocking voltage (typical values)**

**Figure 12. Acceptable repetitive peak off-state voltage versus case to ambient thermal resistance**

**Figure 13. Thermal resistance junction to ambient versus copper surface under tab**


## 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 2.1 D<sup>2</sup>PAK package information

Figure 14. D<sup>2</sup>PAK package outline




(1) Resin gate is accepted in each of position shown on the drawing, or their symmetrical.

**Table 5. D<sup>2</sup>PAK package mechanical data**

| Ref. | Dimensions  |      |       |                       |        |        |
|------|-------------|------|-------|-----------------------|--------|--------|
|      | Millimeters |      |       | Inches <sup>(1)</sup> |        |        |
|      | Min.        | Typ. | Max.  | Min.                  | Typ.   | Max.   |
| A    | 4.30        |      | 4.60  | 0.1693                |        | 0.1811 |
| A1   | 2.49        |      | 2.69  | 0.0980                |        | 0.1059 |
| A2   | 0.03        |      | 0.23  | 0.0012                |        | 0.0091 |
| A3   |             | 0.25 |       |                       | 0.0098 |        |
| b    | 0.70        |      | 0.93  | 0.0276                |        | 0.0366 |
| b2   | 1.25        |      | 1.7   | 0.0492                |        | 0.0669 |
| c    | 0.45        |      | 0.60  | 0.0177                |        | 0.0236 |
| c2   | 1.21        |      | 1.36  | 0.0476                |        | 0.0535 |
| D    | 8.95        |      | 9.35  | 0.3524                |        | 0.3681 |
| D1   | 7.50        |      | 8.00  | 0.2953                |        | 0.3150 |
| D2   | 1.30        |      | 1.70  | 0.0512                |        | 0.0669 |
| e    | 2.54        |      |       | 0.1                   |        |        |
| E    | 10.00       |      | 10.28 | 0.3937                |        | 0.4047 |
| E1   | 8.30        |      | 8.70  | 0.3268                |        | 0.3425 |
| E2   | 6.85        |      | 7.25  | 0.2697                |        | 0.2854 |
| G    | 4.88        |      | 5.28  | 0.1921                |        | 0.2079 |
| H    | 15          |      | 15.85 | 0.5906                |        | 0.6240 |
| L    | 1.78        |      | 2.28  | 0.0701                |        | 0.0898 |
| L2   | 1.27        |      | 1.40  | 0.0500                |        | 0.0551 |
| L3   | 1.40        |      | 1.75  | 0.0551                |        | 0.0689 |
| R    |             | 0.40 |       |                       | 0.0157 |        |
| V2   | 0°          |      | 8°    | 0°                    |        | 8°     |


1. Dimensions in inches are given for reference only

**Figure 15. D<sup>2</sup>PAK recommended footprint (dimensions are in mm)**


## 2.2 TO-220AB package information

- Molding compound resin is halogen-free and meets flammability standard UL94 level 0
- Lead-free package leads finishing
- **ECOPACK2** compliant
- Recommended torque: 0.4 to 0.6 N.m

**Figure 16. TO-220AB package outline**




(1) Resin gate position accepted in one of the two positions or in the symmetrical opposites.

**Table 6. TO-220AB package mechanical data**

| Ref. | Dimensions  |       |       |                       |        |        |
|------|-------------|-------|-------|-----------------------|--------|--------|
|      | Millimeters |       |       | Inches <sup>(1)</sup> |        |        |
|      | Min.        | Typ.  | Max.  | Min.                  | Typ.   | Max.   |
| A    | 15.20       |       | 15.90 | 0.5984                |        | 0.6260 |
| a1   |             | 3.75  |       |                       | 0.1476 |        |
| a2   | 13.00       |       | 14.00 | 0.5118                |        | 0.5512 |
| B    | 10.00       |       | 10.40 | 0.3937                |        | 0.4094 |
| b1   | 0.61        |       | 0.88  | 0.0240                |        | 0.0346 |
| b2   | 1.23        |       | 1.32  | 0.0484                |        | 0.0520 |
| C    | 4.40        |       | 4.60  | 0.1732                |        | 0.1811 |
| c1   | 0.49        |       | 0.70  | 0.0193                |        | 0.0276 |
| c2   | 2.40        |       | 2.72  | 0.0945                |        | 0.1071 |
| e    | 2.40        |       | 2.70  | 0.0945                |        | 0.1063 |
| F    | 6.20        |       | 6.60  | 0.2441                |        | 0.2598 |
| I    | 3.73        |       | 3.88  | 0.1469                |        | 0.1528 |
| L    | 2.65        |       | 2.95  | 0.1043                |        | 0.1161 |
| l2   | 1.14        |       | 1.70  | 0.0449                |        | 0.0669 |
| l3   | 1.14        |       | 1.70  | 0.0449                |        | 0.0669 |
| l4   | 15.80       | 16.40 | 16.80 | 0.6220                | 0.6457 | 0.6614 |
| M    |             | 2.6   |       |                       | 0.1024 |        |

1. Inch dimensions are for reference only.

### 3 Ordering information

**Figure 17. Ordering information scheme**

**Table 7. Ordering information**

| Order code   | Marking   | Package            | Weight | Base qty. | Delivery mode     |
|--------------|-----------|--------------------|--------|-----------|-------------------|
| T2035H-6G    | T2035H-6G | D <sup>2</sup> PAK | 1.5 g  | 50        | Tube              |
| T2035H-6G-TR | T2035H-6G |                    |        | 1000      | Tape and reel 13" |
| T2035H-6I    | T2035H-6I | TO-220AB Ins.      | 2.3 g  | 50        | Tube              |
| T2035H-6T    | T2035H-6T | TO-220AB           | 2.3 g  | 50        | Tube              |
| T2050H-6G    | T2050H-6G | D <sup>2</sup> PAK | 1.5 g  | 50        | Tube              |
| T2050H-6G-TR | T2050H-6G |                    |        | 1000      | Tape and reel 13" |
| T2050H-6T    | T2050H-6T | TO-220AB           | 2.3 g  | 50        | Tube              |

## Revision history

**Table 8. Document revision history**

| Date        | Version | Changes                                                                                                                                                                                                                                                                                                            |
|-------------|---------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 31-May-2007 | 1       | First issue.                                                                                                                                                                                                                                                                                                       |
| 19-Sep-2011 | 2       | Added TO-220AB Ins and D <sup>2</sup> PAK packages. Reformatted to current standards.                                                                                                                                                                                                                              |
| 08-Aug-2011 | 3       | Updated: Features and Description. Removed order code T20xxH-6G from Figure 14 and Table 8.                                                                                                                                                                                                                        |
| 05-Jan-2017 | 4       | Updated Figure 4: "Variation of thermal impedance versus pulse duration" , Figure 7: "Non-repetitive surge peak on-state current for a sinusoidal pulse", Section 6.2: "D <sup>2</sup> PAK package information", Section 6.3: "TO-220AB (NIns. and Ins.) package information" and Table 8: "Ordering information". |
| 02-Oct-2019 | 5       | Updated description title. Minor text changed.                                                                                                                                                                                                                                                                     |
| 06-Aug-2021 | 6       | Updated <a href="#">Table 2</a> .                                                                                                                                                                                                                                                                                  |



**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics – All rights reserved