




PRODUCT NBR	DIM "L"	DIM "W"	QUANTITY PER REEL
77727-X01(LF)	2.3	14.1	36000
77727-X02(LF)	4.3	16.1	36000
77727-X11(LF)	2.3	14.1	5000
77727-X12(LF)	4.3	16.1	5000
77727-X21(LF)	2.3	14.1	72000
77727-X22(LF)	4.3	16.1	72000

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 3



REELING DIRECTION




NOTES :

- 1 - MATERIAL : PHOSPHOR BRONZE ACC DIN 17670 CuSn6F65
- 2 - FOR APPLICATION DATA SEE TA 343
- 3 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - c - LEGAL STATEMENT: SEE GS-22-008

77727-4XXLF	1.27µm Ni	1.27µm Ni	2-8µmSn	2-4µm Sn
77727-4XX	0.1-0.5µm Ni	0.1-0.5µm Ni	1-8µmSnPb	1-4µm SnPb
CODE X PLATING	AREA "C" UNDERPLATING ON BOTH SIDES	AREA "D" OVERPLATING ON BOTH SIDES	AREA "C" OVERPLATING ON BOTH SIDES	AREA "D" OVERPLATING ON BOTH SIDES

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code SEE NOTE 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUFLEX										
ltr	ecn no	dr	date	tolerances unless		otherwise specified				title BERG DUFLEX SOLDER TAB										
C	F80386	DLE	98.07.15	angles	linear	±0.13														
D	F04-0373	DLE	04.11.22																	
E	F05-0286	DLE	05.11.07			±2°														
F	F06-0214	DLE	06.06.30	dr	D LEGRAND		98.07.15				dwg no				sheet 1 of 1				size	
G	F07-0165	DLE	07.03.30	engr	JM PHAMVAN		98.07.15				77727				A3					
				chr	P NIZZI		98.07.15													
				appd	JM PHAMVAN		98.07.15													
sheet index		revision		G																
		sheet		1																

form: A3

Copyright FCI

FCI
FCIconnect.com