

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED

LOC	
-----	--

DIST	
------	--

REVISIONS

P	LTR
---	-----

--	--

DESCRIPTION

DATE _____

D/WN	AI
------	----

PVD


A1

REVISÉ PER ECO-11-004820

11MAR





















RK	H
----	---


















MF



RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381[.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
6. FINISH: 0.000381[.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.

	101.19 [3.984]	99.06 [3.900]	39	40	9-146481-0
	98.65 [3.884]	96.52 [3.800]	38	39	8-146481-9
	96.11 [3.784]	93.98 [3.700]	37	38	8-146481-8
	93.57 [3.684]	91.44 [3.600]	36	37	8-146481-7
	91.03 [3.584]	88.90 [3.500]	35	36	8-146481-6
	88.49 [3.484]	86.36 [3.400]	34	35	8-146481-5
	85.95 [3.384]	83.82 [3.300]	33	34	8-146481-4
	83.41 [3.284]	81.28 [3.200]	32	33	8-146481-3
	80.87 [3.184]	78.74 [3.100]	31	32	8-146481-2
	78.33 [3.084]	76.20 [3.000]	30	31	8-146481-1
	75.79 [2.984]	73.66 [2.900]	29	30	8-146481-0
	73.25 [2.884]	71.12 [2.800]	28	29	7-146481-9
	70.71 [2.784]	68.58 [2.700]	27	28	7-146481-8
	68.17 [2.684]	66.04 [2.600]	26	27	7-146481-7
	65.63 [2.584]	63.50 [2.500]	25	26	7-146481-6
	63.09 [2.484]	60.96 [2.400]	24	25	7-146481-5
	60.55 [2.384]	58.42 [2.300]	23	24	7-146481-4
	58.01 [2.284]	55.88 [2.200]	22	23	7-146481-3
	55.47 [2.184]	53.34 [2.100]	21	22	7-146481-2
	52.93 [2.084]	50.80 [2.000]	20	21	7-146481-1
	50.39 [1.984]	48.26 [1.900]	19	20	7-146481-0
	47.85 [1.884]	45.72 [1.800]	18	19	6-146481-9
	45.31 [1.784]	43.18 [1.700]	17	18	6-146481-8
	42.77 [1.684]	40.64 [1.600]	16	17	6-146481-7
	40.23 [1.584]	38.10 [1.500]	15	16	6-146481-6
	37.69 [1.484]	35.56 [1.400]	14	15	6-146481-5
	35.15 [1.384]	33.02 [1.300]	13	14	6-146481-4
	32.61 [1.284]	30.48 [1.200]	12	13	6-146481-3
	30.07 [1.184]	27.94 [1.100]	11	12	6-146481-2
	27.53 [1.084]	25.40 [1.000]	10	11	6-146481-1
	24.99 [.984]	22.86 [.900]	9	10	6-146481-0
	22.45 [.884]	20.32 [.800]	8	9	5-146481-9
	19.91 [.784]	17.78 [.700]	7	8	5-146481-8
	17.37 [.684]	15.24 [.600]	6	7	5-146481-7
	14.83 [.584]	12.70 [.500]	5	6	5-146481-6
	12.29 [.484]	10.16 [.400]	4	5	5-146481-5
	9.75 [.384]	7.62 [.300]	3	4	5-146481-4
	7.21 [.284]	5.08 [.200]	2	3	5-146481-3
	4.67 [.184]	2.54 [.100]	1	2	5-146481-2
	2.13 [.084]	-	-	1	5-146481-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

	101.19 [3.984]	99.06 [3.900]	39	40	4-146481-0
	98.65 [3.884]	96.52 [3.800]	38	39	3-146481-9
	96.11 [3.784]	93.98 [3.700]	37	38	3-146481-8
	93.57 [3.684]	91.44 [3.600]	36	37	3-146481-7
	91.03 [3.584]	88.90 [3.500]	35	36	3-146481-6
	88.49 [3.484]	86.36 [3.400]	34	35	3-146481-5
	85.95 [3.384]	83.82 [3.300]	33	34	3-146481-4
	83.41 [3.284]	81.28 [3.200]	32	33	3-146481-3
	80.87 [3.184]	78.74 [3.100]	31	32	3-146481-2
	78.33 [3.084]	76.20 [3.000]	30	31	3-146481-1
	75.79 [2.984]	73.66 [2.900]	29	30	3-146481-0
	73.25 [2.884]	71.12 [2.800]	28	29	2-146481-9
	70.71 [2.784]	68.58 [2.700]	27	28	2-146481-8
	68.17 [2.684]	66.04 [2.600]	26	27	2-146481-7
	65.63 [2.584]	63.50 [2.500]	25	26	2-146481-6
	63.09 [2.484]	60.96 [2.400]	24	25	2-146481-5
	60.55 [2.384]	58.42 [2.300]	23	24	2-146481-4
	58.01 [2.284]	55.88 [2.200]	22	23	2-146481-3
	55.47 [2.184]	53.34 [2.100]	21	22	2-146481-2
	52.93 [2.084]	50.80 [2.000]	20	21	2-146481-1
	50.39 [1.984]	48.26 [1.900]	19	20	2-146481-0
	47.85 [1.884]	45.72 [1.800]	18	19	1-146481-9
	45.31 [1.784]	43.18 [1.700]	17	18	1-146481-8
	42.77 [1.684]	40.64 [1.600]	16	17	1-146481-7
	40.23 [1.584]	38.10 [1.500]	15	16	1-146481-6
	37.69 [1.484]	35.56 [1.400]	14	15	1-146481-5
	35.15 [1.384]	33.02 [1.300]	13	14	1-146481-4
	32.61 [1.284]	30.48 [1.200]	12	13	1-146481-3
	30.07 [1.184]	27.94 [1.100]	11	12	1-146481-2
	27.53 [1.084]	25.40 [1.000]	10	11	1-146481-1
	24.99 [.984]	22.86 [.900]	9	10	1-146481-0
	22.45 [.884]	20.32 [.800]	8	9	146481-9
	19.91 [.784]	17.78 [.700]	7	8	146481-8
	17.37 [.684]	15.24 [.600]	6	7	146481-7
	14.83 [.584]	12.70 [.500]	5	6	146481-6
	12.29 [.484]	10.16 [.400]	4	5	146481-5
	9.75 [.384]	7.62 [.300]	3	4	146481-4
	7.21 [.284]	5.08 [.200]	2	3	146481-3
	4.67 [.184]	2.54 [.100]	1	2	146481-2
	2.13 [.084]	-	-	1	146481-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT

DWN 14-MAR-97
F BRANDBERG

CHK 14-MAR-97

APVD	14-MAR-97
------	-----------

G. DUBNICZKI
PRODUCT SPEC

APPLICATION SPEC

—



TE Connectivity

HEADER ASSEMBLY, MOD II,

STACK

.025 SQ

SIZE	CAGE CODE	DRAWING NO
------	-----------	------------

ING, SINGLE ROW,