


PIN STYLE	NB OF POS	PRODUCT DEFINITION				TOP VIEW OF HEADER SHOWING MISSING PIN POSITIONS							
		"A" ±0.2	"B" ±0.35	"C" REF	"J" REF	1	5	10	15	20	25	30	35
31	1x 7	5.72	3.45	1.4	9.65								
34	1x 5	5.72	3.45	1.4	9.65								
38	1x 13	5.72	3.45	1.4	9.65								
39	1x 9	5.72	5.99	3.94	12.19								
43	1x 9	5.72	5.99	3.94	12.19								
52	1x 11	5.72	3.45	1.4	9.66								
53	1x 5	5.72	15.27	1.4	9.65								
56	1x 6	6.75	2.9	1.4	10.69								
57	1x 3	15.00	3.05	1.4	18.94								



NOTES:

1. PINS "A" AND "B" USED FOR RETENTION.
2. DIRECTION OF RETENTION SHOWN BY ARROWS.
3. PINS "B" IN MID-POS'N OF HEADER USE THE 4 PINS CONFIGURATION ON ALL HEADERS RANCING FROM 4 TO 36 POS.
4. RETENTION VERSI ONLY AVAILABLE WHEN DIM "B" IS BETWEEN 3 AND 3.5mm
5. RETENTION FEATURE NOT AVAILABLE ON 2 AND 3 POSITIONS HEADER.

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
AE	F09-0038	JCO	09.04.23	angles	linear		HEADER,SR,RA
AF	B-19925	BVE	15.01.08			scale 5/1	POL, 2.54MM
AA	F500093	JMC	95.02.06	dr	LETOY G	91.10.09	dwg no
AB	F50277	JMC	95.04.11	enr	PHAMVAN JM	95.02.06	sheet 2 of 2
AC	F05-0186	LMU	05.05.11	chr	COMPAGNON J	95.02.06	size
AD	F06-0127	LMU	06.02.16	appd	JCO	09.04.23	A3
sheet	revision	AN	AF				type
index	sheet	1	2				CUSTOMER Drawing