





A



B



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PV00
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PV00
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PV00
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PV00

Plating: 4 --> flash AU

Plating: 6 --> 0.76μ AU

C

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PV00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PV00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PV00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PV00LF


Plating: 4 --> flash AU

Plating: 6 --> 0.76μ AU

D

PC card drilling dimensions(after plating)

(thickness 1.60±0.20mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	JOUBERT	1996/09/10	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2			
Eng	PESSON	1996/09/10			0.XX	±0.1					
Chr	LEGARE	1996/09/10			0.XX	±0.1					
Appr	LEGARE	1996/09/10	0.XX	±0.1	ECN		L506-0097				
			Product family				D-SUB		Spec ref -		
			FEMALE CONNECTOR STD EURO			dwg no C01-8646-0493			Rev. D		
title straight solder type for											
catalog no			-			CUSTOMER			sheet 1 of 1		

A

B

C

D