

Insulated Tools

Klein insulated tools combine excellent functionality along with reduction of risk of injury where a tool might make contact with an energized source with voltage up to 1000 volts.



For Professionals...
Since 1857™

Electrician's Insulated Tools

FORGED STEEL

from Klein's US-made, proprietary blend

Durable, three component molded insulation provides protection against electric shock

Induction hardened cutting knives for long life

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool

Forged steel handle

Hot-riveted joint ensures smooth action and no handle wobble

Multi-color, sleek design with small thumb guards for ease of handling and storage

A flame retardant, impact-resistant, multi-color outer coating



Klein electrician's insulated tools meet or exceed IEC 60900: 2012, ASTM F1505, and VDE standards and are clearly marked with the official 1000-volt rating symbol.

2000™ series pliers available.
HEAVY-DUTY CUTTING Cuts ACSR, screws, nails, and most hardened wire

The Electrician's line of insulated tools provides a multi-color, sleeker design than the Classic Lineman's insulated tools. 1000V rated and individually tested to conform to ASTM F1505, IEC 60900. EINS tools have passed VDE third party testing certification to the IEC 60900 standard. This line of tools provides the everyday protection the electrician needs in a compact, lightweight design.

Catalog numbers for Klein electrician's insulated tools have the suffix "EINS" and are marked with the official international 1000-volt rating symbol. Not all tools with plastic coatings or plastic handles provide protection against electrical shock. **Only use those tools that are marked with the official international 1000-volt rating symbol, as shown, if there is any chance that the tool will make contact with an energized source. Product numbers with the EINS suffix contain these warnings below and must be understood.**

⚠ WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



⚠ WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

⚠ WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠ WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠ WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.





Electrician's Insulated Pliers

Electrician's Insulated High-Leverage Side-Cutting Pliers

Additional Features:

- High-leverage design provides 46% greater cutting and gripping power than other plier designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws
- 2000 Series cuts ACSR, screws, nails and most hardened wires



213-9NE-EINS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Weight
213-8NE-EINS	New England	8-13/16" (223.8 mm)	1-7/16" (36.5 mm)	1-7/64" (28.2 mm)	5/8" (15.9 mm)	3/4" (19.1 mm)	1.0 lbs. (0.45 kg)
213-9NE-EINS	New England	9-5/8" (244.5 mm)	1-19/32" (40.5 mm)	1-5/16" (33.3 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	1.3 lbs. (0.59 kg)
2000 Series* – Heavy-duty cutting knives							
2000-9NE-EINS	New England	9-5/8" (244.5 mm)	1-19/32" (40.5 mm)	1-5/16" (33.3 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	1.3 lbs. (0.59 kg)

*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

Electrician's Insulated High-Leverage Diagonal Cutting Pliers

2000 series™

Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other pliers designs
- Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish
- 13° angled head for easier work in confined spaces (Cat. No. 2000-48-EINS)



2000-28-EINS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Weight
2000-28-EINS	Tapered	8-1/4" (209.6 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	11.2 oz. (318 g)
2000-48-EINS	Angled	8-1/4" (209.6 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	11.2 oz. (318 g)

Electrician's Insulated Long-Nose Pliers - Side-Cutting

Additional Features:

- Induction-hardened cutting knives for long life
- Knurled jaws for sure wrapping and looping
- Cat. No. 203-8-EINS features heavier design for easier, more comfortable cutting and extended handle for added reach and leverage
- Cat. Nos. 203-6-EINS and 203-7-EINS has curved handles to provide greater tool control



203-8-EINS



203-7-EINS

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Weight
Heavier Design							
203-8-EINS	8-7/8" (225.4 mm)	2-5/16" (58.7 mm)	1" (25.4 mm)	1/2" (12.7 mm)	5/8" (15.9 mm)	1/8" (3.2 mm)	11.2 oz. (318 g)
Standard Design							
203-6-EINS	6-7/8" (174.6 mm)	1-15/16" (49.2 mm)	11/16" (17.5 mm)	3/8" (9.5 mm)	1/2" (12.7 mm)	3/32" (2.4 mm)	4.8 oz. (136 g)
203-7-EINS	7-3/8" (187.3 mm)	2-7/16" (61.9 mm)	11/16" (17.5 mm)	3/8" (9.5 mm)	1/2" (12.7 mm)	3/32" (2.4 mm)	4.8 oz. (136 g)

Electrician's Insulated Pliers

Electrician's Insulated Combination Pliers

Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals
- Toothed pipe-grip for greater power



12098-EINS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Weight
12098-EINS	Universal	8-7/8" (225.4 mm)	1-25/32" (45.2 mm)	1-1/32" (26.2 mm)	1/2" (12.7 mm)	3/4" (19.1 mm)	1.0 lbs. (0.45 kg)

Electrician's Insulated Pump Pliers

Additional Features:

- Secure tongue and groove design for non-slip grip - even with heavy pressure



502-10-EINS

Cat. No.	Overall Length	Max. Jaw Capacity	Weight
502-10-EINS	10-1/4" (260.4 mm)	1-3/4" (44.5 mm)	1.0 lbs. (0.45 kg)

Electrician's Insulated Cable Cutter

Electrician's Insulated High-Leverage Cable Cutter

Additional Features:

- High-leverage design for exceptional cutting capability
- Cable-gripping shear-type jaws
- Precision, one-hand shearing action
- Perfect for working in confined spaces
- Do NOT use to cut steel or ACSR



63050-EINS

Cat. No.	Overall Length	Maximum Cable Cutting Capacity	Weight
63050-EINS	9-5/8" (244.5 mm)	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	1.0 lbs. (0.45 kg)

Electrician's Insulated Stripper/Cutter

Electrician's Insulated Solid & Stranded Stripper/Cutter

Additional Features:

- Cuts, strips, loops and gauges both solid and stranded wire
- Spring-loaded for self-opening
- Serrated nose for easy bending, shaping and pulling of wire
- Cleanly shears 6-32 and 8-32 screws
- Do not use for cutting steel wire

KLEIN-KURVE
SOLID
8 - 16 AWG

STRANDED
10 - 18 AWG


11054-EINS

Cat. No.	Overall Length	Strips and Cuts	Weight
11054-EINS	8" (203.2 mm)	8 - 16 AWG Solid (8.4 mm ² - 1.3 mm ²), 10 - 18 AWG Stranded (5.3 mm ² - 0.82 mm ²)	8.0 oz. (227 g)



Classic Insulated Tools

FORGED STEEL

from Klein's US-made, proprietary blend



Integral guards help prevent hand contact with conductive parts

Induction hardened cutting knives for long life

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool

Forged steel handle



Hot-riveted joint ensures smooth action and no handle wobble

pliers available.

Cuts ACSR, screws, nails, and most hardened wire

All Classic Klein insulated tools comply with ASTM F-1505 and IEC 60900-2004 standards for insulated tools and are clearly marked with the official international 1000-volt rating symbol. Not all tools with plastic coatings or plastic handles provide protection against electrical shock. The large, bright orange handles make the tool comfortable to use all day and easy to identify in the field. **Only use those tools that are marked with the official international 1000-volt rating symbol, as shown, if there is any chance that the tool will make contact with an energized source. Product numbers with the INS suffix contain these warnings and must be understood.**

▲WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



▲WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

▲WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

▲WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

▲WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

Insulated High-Leverage Side-Cutting Pliers

Additional Features:

- High-leverage design provides 46% greater cutting and gripping power than other plier designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws



D213-9NE-INS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Weight
D213-9NE-INS	New England	9-5/8" (244.5 mm)	1-19/32" (40.5 mm)	1-5/16" (33.3 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	1.3 lbs. (0.59 kg)
2000 Series* – Heavy-duty cutting knives							
D2000-9NE-INS	New England	9-5/8" (244.5 mm)	1-19/32" (40.5 mm)	1-5/16" (33.3 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	25/32" (19.8 mm)

*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

Insulated High-Leverage Side-Cutting Pliers - Connector Crimping

Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals
- High-leverage design provides 46% greater cutting and gripping power than other plier designs
- Streamlined design with sure-gripping, cross-hatched knurled jaws



D213-9NECR-INS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Weight
D213-9NE-CR-INS	New England	9-5/8" (244.5 mm)	1-19/32" (40.5 mm)	1-5/16" (33.3 mm)	5/8" (15.9 mm)	25/32" (19.8 mm)	1.3 lbs. (0.59 kg)



Insulated Pliers – Classic

Insulated High-Leverage Universal Side-Cutting Pliers - Connector Crimping

Additional Features:

- Crimping die behind hinge for superior leverage crimping non-insulated connectors, lugs and terminals
- Toothed pipe-grip for greater power



12098-INS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Weight
12098-INS	Universal	8-7/8" (225.4 mm)	1-25/32" (45.2 mm)	1-1/32" (26.2 mm)	1/2" (12.7 mm)	3/4" (19.1 mm)	1.0 lbs. (0.45 kg)

Insulated High-Leverage Diagonal-Cutting Pliers

Additional Features:

- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other pliers designs
- 13° angled head for easier work in confined spaces Cat. Nos. D248-8-INS and D2000-48-INS series



D228-8-INS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Weight
D228-8-INS	Tapered	8-1/4" (209.6 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	11.2 oz. (318 g)
D248-8-INS	Angled	8-1/4" (209.6 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	11.2 oz. (318 g)
2000 Series* – Heavy-duty cutting knives							
D2000-28-INS	Tapered	8-1/4" (209.6 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	11.2 oz. (318 g)
D2000-48-INS	Angled	8-1/4" (209.6 mm)	13/16" (20.6 mm)	1-3/16" (30.2 mm)	7/16" (11.1 mm)	Standard	11.2 oz. (318 g)

*Cuts ACSR, screws, nails, and most hardened wire. Features combination polished and black-oxide finish.

Insulated Heavy-Duty Diagonal-Cutting Pliers - Tapered Nose

Additional Features:

- Heavy-duty tapered nose design
- One-inch deep jaws easily reach into confined spaces



D220-7-INS

Cat. No.	Nose Type	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Weight
D220-7-INS	Tapered	7-7/8" (200.0 mm)	1" (25.4 mm)	31/32" (24.6 mm)	1/2" (12.7 mm)	Standard	11.2 oz. (318 g)

Insulated Long-Nose Pliers - Side-Cutting

Additional Features:

- Knurled jaws for sure wrapping and looping
- Cat. Nos. D203-8-INS and D203-8N has extended handles provide added reach and leverage
- Cat. Nos. D203-6-INS and D203-7-INS have curved handles to provide greater tool control
- Cat. No. D203-8N-INS has skinning hole for No. 12 AWG wire



D203-8N-INS



D203-7-INS

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Knife Length	Weight
Heavier Design							
D203-8-INS	8-7/8" (225.4 mm)	2-5/16" (58.7 mm)	1" (25.4 mm)	1/2" (12.7 mm)	Standard	5/8" (15.9 mm)	11.2 oz. (318 g)
D203-8N-INS	8-7/8" (225.4 mm)	2-5/16" (58.7 mm)	1" (25.4 mm)	1/2" (12.7 mm)	Standard	5/8" (15.9 mm)	11.2 oz. (318 g)
Standard Design							
D203-6-INS	6-7/8" (174.6 mm)	1-15/16" (49.2 mm)	11/16" (17.5 mm)	3/8" (9.5 mm)	Standard	1/2" (12.7 mm)	4.8 oz. (136 g)
D203-7-INS	7-3/8" (187.3 mm)	2-7/16" (61.9 mm)	11/16" (17.5 mm)	3/8" (9.5 mm)	Standard	1/2" (12.7 mm)	4.8 oz. (136 g)



Insulated Pliers – Classic

Insulated Pump Pliers

Additional Features:

- Secure tongue and groove design for non-slip grip - even with heavy pressure

Cat. No.	Overall Length	Max. Jaw Capacity	Weight
D502-10-INS	10-1/4" (260.4 mm)	1-3/4" (44.5 mm)	1.0 lbs. (0.45 kg)



D502-10-INS

Insulated Crimping/Cutting/Stripping Tools – Classic

Insulated Crimping/Cutting Tool

Additional Features:

- Tapered nose design for working in confined spaces
- Crimping dies marked for insulated and non-insulated solderless terminals and connectors
- Accommodates wire from No. 10 to 22 AWG
- Wire cutter in nose

Cat. No.	Overall Length	Crimps	Weight
1005-INS	9-3/4" (247.7 mm)	10 - 22 AWG	1.0 lbs. (0.45 kg)



1005-INS



Insulated High-Leverage Cable Cutter

Additional Features:

- Special, high-leverage design for exceptional cutting capability
- Cable-gripping shear-type jaws
- Precision, one-hand shearing action
- Perfect for working in confined spaces
- Do NOT use to cut steel or ACSR

Cat. No.	Overall Length	Maximum Cable Cutting Capacity	Weight
63050-INS	9-5/8" (244.5 mm)	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	1.0 lbs. (0.45 kg)



63050-INS

Insulated Wire Stripper/Cutters

Additional Features:

- Cuts, strips, loops and gauges wire
- Spring-loaded for self-opening
- Compact, lightweight wire-stripping and cutting tool
- Narrow nose fits into tight places
- Do not use for cutting steel wire or bolts
- Hardened spring steel with precision-ground stripping holes for easy removal of insulation
- Cat. No. 11055-INS cleanly shears 6-32 and 8-32 screws

Cat. No.	Overall Length	Strips and Cuts	Weight
11045-INS	7" (177.8 mm)	10, 12, 14, 16, 18 Solid AWG (4.0 mm ² , 2.5 mm ² , 1.5 mm ² , 1.0 mm ² , 0.75 mm ²)	9.6 lbs. (4.35 kg)
11049-INS	7" (177.8 mm)	8, 10, 12, 14, 16 Stranded AWG (6.0 mm ² , 4.0 mm ² , 2.5 mm ² , 1.5 mm ² , 1.0 mm ²)	9.6 lbs. (4.35 kg)
11055-INS	8" (203.2 mm)	10, 12, 14, 16, 18 AWG Solid (4.0 mm ² , 2.5 mm ² , 1.5 mm ² , 1.0 mm ² , 0.75 mm ²) 12, 14, 16, 18, 20 AWG Stranded (2.5 mm ² , 1.5 mm ² , 1.0 mm ² , 0.82 mm ² , 0.50 mm ²)	12.0 lbs. (5.44 kg)



11049-INS



SOLID
10 - 18 AWG

STRANDED
12 - 20 AWG

KLEIN-KURVE

11055-INS



Insulated Screwdrivers

 **1000 V**

Klein insulated tools meet or exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and are clearly marked with the official 1000-volt rating symbol

FORGED STEEL

from Klein's US-made, proprietary blend

Durable, two layer, molded insulation

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool

Bright orange outer coating is flame and impact resistant

Cushion-Grip handles for greater torque and comfort

Tip-Ident® quickly identifies driver size

MADE IN USA

⚠WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.

 **1000 V**

⚠WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

Product numbers with the INS suffix contain these warnings and must be understood.

⚠WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

Insulated Screwdrivers - Round-Shank

Additional Features:

- Profilated Phillips-tip provides a more consistent geometric symmetry than conventional Phillips-tip screwdrivers
- Square-Recess tips are perfect for electrical, telephone and work in recessed holes and other tight spaces



Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length	Weight
6334INS	Phillips	#1	4" (101.6 mm)	7-3/4" (196.9 mm)	2.1 oz. (60 g)
603-4-INS	Phillips	#2	4" (101.6 mm)	8-5/16" (211.1 mm)	3.2 lbs. (1.45 kg)
6037INS	Phillips	#2	7" (177.8 mm)	11-5/16" (287.3 mm)	4.0 lbs. (1.81 kg)
6337INS	Phillips	#1	7" (177.8 mm)	12-3/8" (314.3 mm)	6.4 lbs. (2.90 kg)
607-3-INS	Cabinet Tip	3/32" (2.4 mm)	3" (76.2 mm)	6-3/4" (171.5 mm)	1.9 lbs. (0.86 kg)
612-4-INS	Cabinet Tip	1/8" (3.2 mm)	4" (101.6 mm)	7-3/4" (196.9 mm)	2.1 oz. (60 g)
601-4-INS	Cabinet Tip	3/16" (4.8 mm)	4" (101.6 mm)	7-3/4" (196.9 mm)	2.1 oz. (60 g)
601-7-INS	Cabinet Tip	3/16" (4.8 mm)	7" (177.8 mm)	10-3/4" (273.1 mm)	2.7 lbs. (1.22 kg)
602-4-INS	Cabinet Tip	1/4" (6.4 mm)	4" (101.6 mm)	8-5/16" (211.1 mm)	3.2 lbs. (1.45 kg)
605-7-INS	Cabinet Tip	1/4" (6.4 mm)	7" (177.8 mm)	11-5/16" (287.3 mm)	4.0 lbs. (1.81 kg)
602-7-INS	Cabinet Tip	5/16" (7.9 mm)	7" (177.8 mm)	12-3/8" (314.3 mm)	6.4 lbs. (2.90 kg)
602-8-INS	Cabinet Tip	3/8" (9.5 mm)	8" (203.2 mm)	13-3/8" (339.7 mm)	8.0 oz. (227 g)
661-4-INS	Square	#1	4" (101.6 mm)	8-5/16" (211.1 mm)	3.2 lbs. (1.45 kg)
661-7-INS	Square	#1	7" (177.8 mm)	11-5/16" (287.3 mm)	3.2 lbs. (1.45 kg)
662-4-INS	Square	#2	4" (101.6 mm)	8-5/16" (211.1 mm)	3.2 lbs. (1.45 kg)
662-7-INS	Square	#2	7" (177.8 mm)	11-5/16" (287.3 mm)	3.2 lbs. (1.45 kg)



2-Piece Insulated 4" (102 mm) Screwdriver Set - Round Shanks



Additional Features:

- Includes one 1/4" (6 mm) cabinet-tip and one #2 Phillips-tip



33532-INS

Cat. No.	Set Contains				Weight
33532-INS					9.6 oz. (272 g)
Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length	
602-4-INS	Cabinet Tip	1/4" (6.4 mm)	4" (101.6 mm)	8-5/16" (211.1 mm)	
603-4-INS	Phillips	#2	4" (101.6 mm)	8-5/16" (211.1 mm)	

9-Piece Insulated Cushion-Grip Screwdriver Set

- Features three sizes of each tip style: cabinet, keystone, and Phillips
- Highly durable, black nylon case features: nylon-zipper closure, polypropylene handles, custom-fitted tool pockets; extra pocket is provided for storage of papers or other items
- Overall dimensions: 15-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33538) available



33528

Cat. No.	Set Contains				Weight
33528					5.4 lbs. (2.45 kg)
Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length	
601-4-INS	Cabinet Tip	3/16" (4.8 mm)	4" (101.6 mm)	7-3/4" (196.9 mm)	
601-7-INS	Cabinet Tip	3/16" (4.8 mm)	7" (177.8 mm)	10-3/4" (273.1 mm)	
612-4-INS	Cabinet Tip	1/8" (3.2 mm)	4" (101.6 mm)	7-3/4" (196.9 mm)	
602-4-INS	Cabinet Tip	1/4" (6.4 mm)	4" (101.6 mm)	8-5/16" (211.1 mm)	
602-7-INS	Cabinet Tip	5/16" (7.9 mm)	7" (177.8 mm)	12-3/8" (314.3 mm)	
602-8-INS	Cabinet Tip	3/8" (9.5 mm)	8" (203.2 mm)	13-3/8" (339.7 mm)	
6334INS	Phillips	#1	4" (101.6 mm)	7-3/4" (196.9 mm)	
603-4-INS	Phillips	#2	4" (101.6 mm)	8-5/16" (211.1 mm)	
6337INS	Phillips	#1	7" (177.8 mm)	12-3/8" (314.3 mm)	
33538	heavy-duty polyester case				



Insulated Nut Drivers

FORGED STEEL

from Klein's US-made, proprietary blend



Klein insulated tools meet or exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and are clearly marked with the official 1000-volt rating symbol

Thick, exceptionally tough, high-dielectric white inner coating is bonded to the tool



Cushion-Grip handles for greater torque and comfort

Durable, two layer, molded insulation

Bright orange outer coating is flame and impact resistant

Hollow shafts make it possible to work on stacked circuit boards or other long bolt applications

Tip-Ident® quickly identifies nut driver size



⚠ WARNING: Only use tools that are marked with the official international 1000-volt rating symbol shown below, if there is any chance that the tools will make contact with an energized source.



⚠ WARNING: Wear approved eye protection. Always inspect your tools before use. Do not use if orange coating cracks, breaks or becomes damaged. Destroy tool if white layer shows through orange layer.

⚠ WARNING: Do NOT touch uninsulated portion of the tool or any conductive object when either might contact an energized source.

⚠ WARNING: Whenever possible, always de-energize lines and equipment prior to working on or around them. Klein insulated tools are designed only to reduce the chance of injury where the tool may make contact with an energized source.

⚠ WARNING: Because moisture, films, or other surface contaminants are conductive, Klein insulated tools must be kept clean, dry, and free of any surface contaminants.

Product numbers with the INS suffix contain these warnings and must be understood.

6" (152 mm) Insulated Hollow-Shaft Nut Drivers

Additional Features:

- Slimmer molded insulation with increased durability



646-5/8-INS



Cat. No.	Color Code	Hex Size	Overall Length	Weight
646-3/16-INS*	Black	3/16"	9-3/4" (247.7 mm)	2.4 lbs. (1.09 kg)
646-1/4-INS	Red	1/4"	9-3/4" (247.7 mm)	3.2 lbs. (1.45 kg)
646-5/16-INS	Yellow	5/16"	9-3/4" (247.7 mm)	3.2 lbs. (1.45 kg)
646-11/32-INS	Green	11/32"	9-3/4" (247.7 mm)	3.2 lbs. (1.45 kg)
646-3/8-INS	Blue	3/8"	10-5/16" (261.9 mm)	4.0 lbs. (1.81 kg)
646-7/16-INS	Brown	7/16"	10-5/16" (261.9 mm)	4.0 lbs. (1.81 kg)
646-1/2-INS	Red	1/2"	11-3/8" (288.9 mm)	5.6 oz. (159 g)
646-9/16-INS	Orange	9/16"	11-3/8" (288.9 mm)	6.4 lbs. (2.90 kg)
646-5/8-INS	Yellow	5/8"	11-3/8" (288.9 mm)	6.4 lbs. (2.90 kg)

*3/16" magnetic nut driver does not have hollow shaft



Insulated Nut Driver Sets

9-Piece Insulated Cushion-Grip Hollow-Shaft Nut Driver Set - 6" (152 mm) Shafts

Additional Features:

- Features assortment of popular sized nut drivers
- Highly durable, black nylon case features: nylon-zipper closure, polypropylene handles, custom-fitted tool pockets; extra pocket is provided for storage of papers or other items
- Overall case dimensions are: 15" W x 12-3/4" L x 3-1/2" D (381 mm x 324 mm x 89 mm)
- Replacement case available Cat. No. 33534



33524

Cat. No.	Set Contains				Weight
33524					6.0 lbs. (2.72 kg)
	Cat. No.	Color Code	Hex Size	Overall Length	
	646-3/16-INS	Black	3/16"	9-3/4" (247.7 mm)	
	646-1/4-INS	Red	1/4"	9-3/4" (247.7 mm)	
	646-5/16-INS	Yellow	5/16"	9-3/4" (247.7 mm)	
	646-11/32-INS	Green	11/32"	9-3/4" (247.7 mm)	
	646-3/8-INS	Blue	3/8"	10-5/16" (261.9 mm)	
	646-7/16-INS	Brown	7/16"	10-5/16" (261.9 mm)	
	646-1/2-INS	Red	1/2"	11-3/8" (288.9 mm)	
	646-9/16-INS	Orange	9/16"	11-3/8" (288.9 mm)	
	646-5/8-INS	Yellow	5/8"	11-3/8" (288.9 mm)	
	33534	Custom heavy-duty Cordura® case			

Cordura® is a registered trademark of INVISTA for durable fabrics.
 *3/16" magnetic nut driver does not have hollow shaft

Insulated Skinning Knife

Insulated Lineman's Skinning Knife

- Molded measuring marks on back of handle to help measure stripping length of wire
- Large molded handle for an easier, more comfortable grip
- Tough, tempered steel blade provides maximum sharpness and durability to withstand frequent cable scoring



1571-INS

Cat. No.	Blade Length	Handle Color	Overall Length	Weight
1571INS	2-3/8" (60.3 mm)	Orange	8-3/4" (222.3 mm)	5.6 oz. (159 g)

Insulated Tool Kits

General-Purpose Insulated 22-Piece Tool Kit

2000™ series

- Case includes three pallets with custom-fitted pockets for each tool, piano-hinged cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items
- Inside dimensions: 7-3/4" W x 14-1/4" D x 8" H (197 mm x 362 mm x 203 mm)
- Overall dimensions: 18-7/8" W x 15-3/8" D x 8-1/4" H (479 mm x 391 mm x 210 mm)
- Replacement case (Cat. No. 33537) available



33527

Cat. No.	Kit Contains	Weight
33527		24.3 lbs. (11.0 2kg)
Cat. No.	Description	
D2000-9NE-INS	9" Side Cutting Pliers Heavy Duty	
12098-INS	Side Cutting Pliers Crimping Insulated	
D2000-28-INS	8" Insulated Diagonal Cutting Pliers	
D2000-48-INS	8" Insulated HD Diagonal Cutting Pliers	
D203-8N-INS	8" Insulated HD Long Nose Pliers	
D220-7-INS	7" Insulated Diagonal Cutting Pliers	
D203-6-INS	6" Insulated Long Nose Cutting Pliers	
D203-7-INS	7" Long Nose Pliers Side Cutting	
601-4-INS	Insulated 3/16" Cabinet - 4" Screwdriver	
601-7-INS	Insulated 3/16" Cabinet - 7" Screwdriver	
612-4-INS	Insulated 1/8" Slotted - 4" Screwdriver	
602-4-INS	Insulated 1/4" Cabinet - 4" Screwdriver	
602-7-INS	Insulated 5/16" Cabinet - 7" Screwdriver	
602-8-INS	Insulated 3/8" Cabinet - 8" Screwdriver	
6334INS	Insulated #1 Phillips - 4" Screwdriver	
603-4-INS	Insulated #2 Phillips - 4" Screwdriver	
6337INS	Insulated #1 Phillips - 7" Screwdriver	
D502-10-INS	10" Pump Pliers, Insulated	
11045-INS	Insulated Wire Stripper and Cutter	
63050-INS	Cable Cutter, Insulated, High Leverage	
1571INS	Lineman's Skinning Knife, Insulated	
1005-INS	Insulated Crimping/Cutting Tool	
33537	Case for Insulated Tool Kit 33527	



Insulated Tool Kits

Utility Insulated 13-Piece Tool Kit

2000TM series

- The custom case includes two pallets with custom-fitted pockets for each tool, piano-hinged case cover has both a combination lock and two key-locked latches for security, storage space behind the pallets to keep important papers and accessory items
- Inside dimensions: 17-3/4" W x 14-1/4" D x 8" H (451 mm x 362 mm x 203 mm)
- Overall dimensions: 18-7/8" W x 15-3/8" D x 8-1/4" H (79 mm x 391 mm x 210 mm)
- Replacement case (Cat. No. 33535) available



33525

Cat. No.	Kit Contains	Weight
33525		20.1 lbs. (9.12 kg)
Cat. No.	Description	
D2000-9NE-INS	9" Side Cutting Pliers Heavy Duty	
D2000-28-INS	8" Insulated Diagonal Cutting Pliers	
D2000-48-INS	8" Insulated HD Diagonal Cutting Pliers	
D203-8-INS	8" Insulated Long Nose Cutting Pliers	
602-4-INS	Insulated 1/4" Cabinet - 4" Screwdriver	
602-7-INS	Insulated 5/16" Cabinet - 7" Screwdriver	
602-8-INS	Insulated 3/8" Cabinet - 8" Screwdriver	
6334INS	Insulated #1 Phillips - 4" Screwdriver	
603-4-INS	Insulated #2 Phillips - 4" Screwdriver	
6337INS	Insulated #1 Phillips - 7" Screwdriver	
63050-INS	Cable Cutter, Insulated, High Leverage	
D502-10-INS	10" Pump Pliers, Insulated	
1571INS	Lineman's Skinning Knife, Insulated	
33535	Case for Utility Tool Kit 33525	

Utility Insulated 13-Piece Tool Kit with Roll-up Case

2000TM series

- The light, compact, soft roll-up carry case provides protective storage with custom-fitted pockets for each tool
- Kit includes a padded, adjustable shoulder strap
- Case dimensions: Opened 24-1/2" x 24-1/2" (622 mm x 622 mm), Closed 24-1/2" x 5-1/2" (622 mm x 140 mm)
- Replacement roll-up case (Cat. No. 33535SC) available



33525SC

Cat. No.	Kit Contains	Weight
33525SC		9.8 lbs. (4.45 kg)
Cat. No.	Description	
D2000-9NE-INS	9" Side Cutting Pliers Heavy Duty	
D2000-28-INS	8" Insulated Diagonal Cutting Pliers	
D2000-48-INS	8" Insulated HD Diagonal Cutting Pliers	
D203-8-INS	8" Insulated Long Nose Cutting Pliers	
602-4-INS	Insulated 1/4" Cabinet - 4" Screwdriver	
602-7-INS	Insulated 5/16" Cabinet - 7" Screwdriver	
602-8-INS	Insulated 3/8" Cabinet - 8" Screwdriver	
6334INS	Insulated #1 Phillips - 4" Screwdriver	
603-4-INS	Insulated #2 Phillips - 4" Screwdriver	
6337INS	Insulated #1 Phillips - 7" Screwdriver	
63050-INS	Cable Cutter, Insulated, High Leverage	
D502-10-INS	10" Pump Pliers, Insulated	
1571INS	Lineman's Skinning Knife, Insulated	
33535SC	Case for Utility Tool Kit 33525SC	



Insulated Tool Kits

Premium Insulated 8-Piece Tool Kit

2000™ series

- Cat. No. D2000-9NE-INS and D2000-48-INS cut ACSR, screws, nails and most hardened wire
- Highly durable, black nylon case features: nylon-zipper closure, polypropylene handles, custom-fitted tool pockets
- Overall case dimensions are: 15-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33536) available

Cat. No.	Kit Contains	Weight
33529		6.9 lbs. (3.13 kg)
Cat. No.	Description	
D2000-9NE-INS	9" Side Cutting Pliers Heavy Duty	
D2000-48-INS	8" Insulated HD Diagonal Cutting Pliers	
D203-8N-INS	8" Insulated HD Long Nose Pliers	
601-6-INS	Insulated 3/16" Cabinet - 6" Screwdriver	
602-4-INS	Insulated 1/4" Cabinet - 4" Screwdriver	
603-4-INS	Insulated #2 Phillips - 4" Screwdriver	
63050-INS	Cable Cutter, Insulated, High Leverage	
11055-INS	Klein-Kurve® Wire Stripper Insulated	
33536	Case for Insulated Tool Kit 33529	

See individual tool listings for more details.



33529

Basic Insulated 8-Piece Tool Kit

- Highly durable, black nylon case features: nylon-zipper closure, polypropylene handles, custom-fitted tool pockets
- Overall case dimensions are: 15-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33536) available

Cat. No.	Kit Contains	Weight
33526		6.9 lbs. (3.13 kg)
Cat. No.	Description	
D213-9NE-INS	9" Insulated Side Cutting Pliers	
D228-8-INS	8" Insulated, Diagonal-Cutters	
D203-8N-INS	8" Insulated HD Long Nose Pliers	
601-6-INS	Insulated 3/16" Cabinet - 6" Screwdriver	
602-4-INS	Insulated 1/4" Cabinet - 4" Screwdriver	
603-4-INS	Insulated #2 Phillips - 4" Screwdriver	
63050-INS	Cable Cutter, Insulated, High Leverage	
11045-INS	Insulated Wire Stripper and Cutter	
33536	Case for Insulated Tool Kit 33529	

See individual tool listings for more details.



33526