



Plug-in type



PC board type

RoHS compliant

FEATURES

- **Micro-ISO type terminals**
- **Small size:**
20 mm(L)×15 mm(W)×22 mm(H)
.787 inch(L)×.591 inch(W)×.866 inch(H)
- **Wide line-up**
PC board and Plug-in type, Resistor inside type.
24V DC type is also available.
- **Compact and high-capacity 35A load switching**
N.O.: 35A 14V DC, N.C.: 20A 14V DC (Sealed type)
Min. 5×10^4
N.O.: 35A 14V DC, N.C.: 20A 14V DC (Flux-resistant type)
Min. 10^5 *12V DC type

- **Uses international standard ISO terminal arrangement.**

The ISO international standard terminal arrangement is used.

TYPICAL APPLICATIONS

- Fan motor
- Heater
- Head lamp
- Air Compressor
- ABS
- Blower fan
- Defogger, etc.

ORDERING INFORMATION

CM - - - -

Contact arrangement

1a: 1 Form A

1: 1 Form C

Protective construction

Nil: Sealed type

F: Flux-resistant type

Protective element

Nil: None (Standard type)

R: With resistor inside

Mounting classification

Nil: Plug-in type

P: PC board type (24 V only)

Coil voltage (DC)

12 V, 24 V

TYPES

Standard type

Contact arrangement	Coil voltage	Plug-in type		PC board type	
		Sealed type	Flux-resistant type	Sealed type	Flux-resistant type
		Part No.	Part No.	Part No.	Part No.
1 Form A	12 V DC	CM1a-12V	CM1aF-12V	—	—
	24 V DC	CM1a-24V	CM1aF-24V	CM1a-P-24V	CM1aF-P-24V
1 Form C	12 V DC	CM1-12V	CM1F-12V	—	—
	24 V DC	CM1-24V	CM1F-24V	CM1-P-24V	CM1F-P-24V

Standard packing; Carton: 50 pcs.; Case: 200 pcs.

Note: Please use "CM*-R-*-*" built-in resistor type. (Asterisks "*" should be filled in from ORDERING INFORMATION.)

CM

RATING

1. Coil data

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Usable voltage range
12 V DC	3 to 7 V DC	1.2 to 4.2 V DC	125 mA	96Ω	1.5 W	10 to 16V DC
24 V DC	6 to 14 V DC	2.4 to 8.4 V DC	75 mA	320Ω	1.8 W	20 to 32V DC

2. Specifications


Characteristics	Item		Specifications			
			12 V DC		24 V DC	
Contact	Arrangement		1 Form A	1 Form C	1 Form A	1 Form C
	Contact resistance (Initial)		Typ 2mΩ (By voltage drop 6V DC 1A)			
	Contact voltage drop (after electrical life test)		N.O.: Max. 0.5 V (By voltage drop 14 V DC 35 A)	N.O.: Max. 0.5 V (By voltage drop 14 V DC 35 A) N.C.: Max. 0.3 V (By voltage drop 14 V DC 20 A)	N.O.: Max. 0.3 V (By voltage drop 28 V DC 15 A)	N.O.: Max. 0.3 V (By voltage drop 28 V DC 15 A) N.C.: Max. 0.2 V (By voltage drop 28 V DC 8 A)
	Contact material		Ag alloy (Cadmium free)			
	Nominal switching capacity (resistive load)		N.O.: 35 A 14V DC	N.O.: 35 A 14V DC N.C.: 20 A 14V DC	N.O.: 15 A 28V DC	N.O.: 15 A 28V DC N.C.: 8 A 28V DC
Rating	Max. carrying current (at 85°C 185°F, continuous)		N.O.: 20 A 14V DC	N.O.: 20 A 14V DC N.C.: 10 A 14V DC	N.O.: 15 A 28V DC	N.O.: 15 A 28V DC N.C.: 8 A 28V DC
	Nominal operating power		1.5 W, 1.7 W (with resistor inside type)		1.8 W, 2.0 W (with resistor inside type)	
	Min. switching capacity (resistive load)*1		1 A 14V DC		1 A 24V DC	
Electrical characteristics	Insulation resistance (Initial)		Min. 20 MΩ (at 500V DC, Measurement at same location as "Breakdown voltage" section.)			
	Breakdown voltage (Initial)	Between open contacts	500 Vrms for 1 min. (Detection current: 10mA)			
		Between contacts and coil	500 Vrms for 1 min. (Detection current: 10mA)			
	Operate time (at nominal voltage) (at 20°C 68°F)		Max. 10ms (excluding contact bounce time) (Initial)			
	Release time (at nominal voltage) (at 20°C 68°F)		Max. 10ms (excluding contact bounce time) (Initial)			
Mechanical characteristics	Shock resistance	Functional	Min. 200 m/s ² {20G} (Half-wave pulse of sine wave: 11ms; detection time: 10μs)			
		Destructive	Min. 1,000 m/s ² {100G} (Half-wave pulse of sine wave: 6ms)			
	Vibration resistance	Functional	10 Hz to 500 Hz, Min. 44.1 m/s ² {4.5G}			
		Destructive	10 Hz to 2,000 Hz, Min. 44.1 m/s ² {4.5G}, Time of vibration for each direction; X, Y, Z direction: 4 hours			
Expected life	Mechanical (at 120 cpm)		Min. 10 ⁶			
	Electrical (operating frequency: 2s ON, 2s OFF)		Flux-resistant type: Min. 10 ⁵ , Sealed type: Min. 5 × 10 ⁴			
Conditions	Conditions for operation, transport and storage*2		Ambient temperature: -40°C to +85°C -40°F to +185°F*3, Humidity: 5% R.H. to 85% R.H. (Not freezing and condensing at low temperature), Air pressure: 86 to 106 kPa			
Mass			Approx. 20 g .71 oz			

Notes: *1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.
*2. The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. Please refer to "Usage ambient condition" in CAUTIONS FOR USE OF AUTOMOTIVE RELAYS.
*3. Please inquire if you will be using the relay in a high temperature atmosphere.

REFERENCE DATA


1.-(1) Coil temperature rise (12V type, 85°C 185°F)

Sample: CM1F-12V, 3 pcs.
Measured portion: Inside the coil
Contact carrying current: 20A, 35A
Ambient temperature: 85°C 185°F




1.-(2) Coil temperature rise (24V type, 85°C 185°F)


Sample: CM1F-24V, 4 pcs.
Measured portion: Inside the coil
Contact carrying current: 0A, 15A
Ambient temperature: 85°C 185°F



2. Ambient temperature and operating voltage range (12V type)




3. Ambient temperature characteristics (Cold/initial)



4. Distribution of pick-up and drop-out voltage


Sample: CM1F-12V, 100pcs.



5. Distribution of operate time

Sample: CM1F-12V, 30pcs.


* Max. 10ms standard (excluding contact bounce)



6. Distribution of release time

Sample: CM1F-12V, 30pcs.

* Max. 10ms standard (excluding contact bounce)



7.-(1) Electrical life test (Motor free)

Sample: CM1aF-R-12V, 6pcs.


Load: 16 A 13.5 V DC

Cooling fan motor actual load (free condition)

Operating frequency: ON 2s, OFF 6s


Ambient temperature: Room temperature

Circuit




Load current waveform


Inrush current: 85A, Steady current: 18A,



Change of pick-up and drop-out voltage




Change of contact resistance




7.-(2) Electrical life test (Halogen lamp load)
Sample: CM1aF-R-12V, 6pcs.
Load: 20A 13.5V DC
Operating frequency: ON 1s, OFF 14s
Ambient temperature: Room temperature

Change of pick-up and drop-out voltage



Change of contact resistance




DIMENSIONS (mm inch)

The CAD data of the products with a **CAD Data** mark can be downloaded from: <http://industrial.panasonic.com/ac/e/>

1. Plug-in type (1 Form C)

CAD Data


External dimensions



Dimension:	General tolerance
Max. 1mm .039 inch:	±0.1 ±.004
1 to 3mm .039 to .118 inch:	±0.2 ±.008
Min. 3mm .118 inch:	±0.3 ±.012

* Intervals between terminals is measured at A surface level.


Schematic (Bottom view)



2. Plug-in type (1 Form A)

CAD Data


External dimensions



Dimension:	General tolerance
Max. 1mm .039 inch:	±0.1 ±.004
1 to 3mm .039 to .118 inch:	±0.2 ±.008
Min. 3mm .118 inch:	±0.3 ±.012

* Intervals between terminals is measured at A surface level.


Schematic (Bottom view)



3. PC board type (1 Form C) *24V only

CAD Data

External dimensions



Dimension:

Max. 1mm .039 inch:

1 to 3mm .039 to .118 inch: $\pm 0.2 \pm .008$


Min. 3mm .118 inch:

General tolerance

 $\pm 0.1 \pm .004$ $\pm 0.2 \pm .008$ $\pm 0.3 \pm .012$


* Dimensions (thickness and width) of terminal is measured before pre-soldering.
Intervals between terminals is measured at A surface level.

Schematic (Bottom view)



\ Including resistor type also available

PC board pattern (Bottom view)




Tolerance: $\pm 0.1 \pm .004$

4. PC board type (1 Form A) *24V only

CAD Data

External dimensions



Dimension:

Max. 1mm .039 inch:

1 to 3mm .039 to .118 inch: $\pm 0.2 \pm .008$


Min. 3mm .118 inch:

General tolerance

 $\pm 0.1 \pm .004$ $\pm 0.2 \pm .008$ $\pm 0.3 \pm .012$

* Dimensions (thickness and width) of terminal is measured before pre-soldering. Intervals between terminals is measured at A surface level.

Schematic (Bottom view)



\ Including resistor type also available

NOTES

1. Soldering

Max. 350°C 662°F (solder temperature),
within 3 seconds (soldering time)

The effect on the relay depends on the actual PC board used. Please verify the PC board to be used.

For general cautions for use, please refer to the “CAUTIONS FOR USE OF AUTOMOTIVE RELAYS”

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

[CM1aF-12V](#) [CM1aF-D-P-12V](#) [CM1aF-R-12V](#) [CM1aF-R-P-12V](#) [CM1a-R-12V](#) [CM1F-12V](#) [CM1F-R-12V](#) [CM1-R-12V](#)
[CM1-12V](#)