

6

5

4

3

2

1

E

E

D

D

C


C

B

B

A

A



NOTES:

MATERIALS:

MOLDED BODY:	BLACK POLYAMIDE
COUPLING NUT:	NI PLATED BRASS
COMPRESSION NUT:	BLACK POLYAMIDE
GROMMETT	NITRILE RUBBER
CONTACTS:	GOLD/NICKEL OVER COPPER ALLOY
INSERT:	BLACK NYLON
INSERT HOUSING:	BLACK POLYAMIDE
SET SCREWS:	NI PLATED BRASS

ELECTRICAL:

CURRENT RATING:	4AMP MAX
VOLTAGE RATING:	250V

MECHANICAL:


TEMPERATURE RANGE:	-20° TO 80°C
INGRESS PROTECTION:	IP 67

AGENCY CERTIFICATIONS:

AGENCY:	cCSAus FILE LR6837
---------	--------------------

TABLE 2 - COMPONENT INFORMATION

ITEM	QTY	DESCRIPTION
1	1	INSULATOR
2	1	COUPLNG NUT
3	1	INSERT BODY
4	1	CONNECTOR BODY
5	1	O-RING
6	1	GROMMET
7	1	COMPRESSION NUT
8	4	SCREW, M3 x 5

UPDATE PER JM EC NO: WNA2009-0313 DRWN: LHARTMAN 2008/10/27 CHKD: VOU 2008/11/07 APPR: JFMURPHY 2008/11/10		DESCRIPTION	QUALITY SYMBOLS <div>▽=0</div> <div>▽C=0</div>	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE ----		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY DATE		TITLE MICRO-CHANGE FIELD ATTCH 4 POLE FEMALE ST FF PG9 FITTING SCREW		
				4 PLACES	±---	±---	LHARTMAN 2008/10/27				
				3 PLACES	±---	±.005	CHECKED BY DATE				
				2 PLACES	±---	±.010	VOU 2008/10/27				
				1 PLACE	±---	±.020	APPROVED BY DATE		molex MOLEX INCORPORATED		
				ANGULAR ±1°			MATERIAL NO. 1200710036		DOCUMENT NO. SD-130044-003		SHEET NO. 1 OF 1
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
					SIZE A						

6

5

4

3

2

1