




Description	Material	Finish
Body	Brass	Nickel
Pin	Brass	Gold
Insulation	PTFE	N/A
Crimp Ring	Brass	Nickel
Cover	Brass	Nickel


REVISIONS			
REV	DESCRIPTION	DATE	APPV
B	Added New Title Block	12-JUL-12	SAH

SIDE VIEW

5/8-24UNEF-2B THREADS



RECOMMENDED CABLE STRIPPING DIMENSIONS



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ALL DIMENSIONS ARE IN INCHES [mm].
2. DIMENSIONS APPLY AFTER FINISHING.
3. MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE.
4. SAFETY BREAK ALL SHARP CORNERS AND EDGES .02 MAXIMUM.

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS DESIGNATED AGENTS.

MATERIAL:

TOLERANCES:  
.020 [0.50]-.200 [5.00]=±.008 [0.20]  
.200 [5.00]-.1200 [30.00]=±.016 [0.40]  
1.20 [30.0]-4.75 [120.0]=±.024 [0.60]  
4.75 [120.0]-12.40 [315.0]=±.040 [1.0]

PROJECTION:



ANGLES: ±1°

FINISH:

DRAWN: B.MURPHY DT: 12-JUL-12

ENGR: S.HOGAN DT: 12-JUL-12

**Linx** 159 ORT LANE  
MERLIN, OR 97532

TITLE:  
N MALE RIGHT ANGLE  
CABLE END CRIMP FOR RG58 CABLE

SIZE	DWG. NO.	REV
A	CONN012-R58	B

DO NOT SCALE DRAWING

SHEET 1 OF 1