


CB5088-000 Product Details



CB5088-000
(HF-11FRX25)

TE Internal Number: CB5088-000



Heat Shrink Tubing

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = HRSR
- Product Source = U.K., U.S.
- Semirigid
- Heavy Wall Style

Documentation & Additional Information

Product Drawings:

- [Customer Drawing](#) (PDF, English)

Catalog Pages/Data Sheets:

- [RAYCHEM_TUBING_CATALOG_SECT1_PRODUCTS_A-H](#) (PDF, English)

Product Specifications:

- [Raychem HF Sleeving Highly Flexible Heat Shrinkable](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Color = Black

Electrical Characteristics:

- Product Source = U.K., U.S.
- [Recovered ID, Max. \(mm \[in\]\)](#) = 8.00 [0.315]
- Product Use = Cables

Dimensions:

- [Expanded ID, Min. \(mm \[in\]\)](#) = 44.45 [1.750]
- Length (M [ft]) = 7.62 [25.00]

Body Features:

- [Product Name](#) = HRSR
- Pliancy = Semirigid
- [Wall Style](#) = Heavy
- [Wall Type](#) = Single
- Material = Polyolefin
- [Shrink Ratio](#) = 5.6:1
- Resistant To = Abrasion, Mechanical Damage
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 2.41 [0.095]

Housing Features:

- Material Systems = No

Industry Standards:

- Government/Industry Qualification = No
- Flammability Rating Type = Flame-Retardant
- UL Rating = None
- CSA Certified = No
- Approved Standards = ABS, DNV, Lloyd's
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Fluid Resistance = None
- [Operating Temperature \(°C\)](#) = -55 - +90

Conditions for Usage:

- Full Recovery Temperature (°C) = 121
- Shrink Temperature, Min. (°C) = 90
- High Temperature Compatible = No

Operation/Application:

- Application = Cable Jacketing, Insulation and Protection
- Emission Free = No

Packaging Features:

- Packaging Method = Piece

Other:

- Brand = Raychem