

Customer Information Sheet

DRAWING No.: M50-315XX42R

IF IN DOUBT - ASK


©

NOT TO SCALE


THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

TAPE DETAILS FOR
15, 20, 22 AND 25 WAYS ONLY




SECTION Y-Y




DETAIL B
SCALE 6



TAPE DETAILS FOR
03, 04, 05, 06, 08 & 10 WAYS ONLY



SECTION Y-Y



SECTION X-X




ORDER CODE:

M50-315XX42R

No. OF CONTACTS PER ROW:
03, 04, 05, 06, 08,
10, 15, 20, 22, 25

FINISH:
42 = GOLD FLASH + 100% TIN OVER NICKEL

REELED PART No.	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	PACK SIZE
M50-3150342R	16.00	7.50	4.55	N/A	1400
M50-3150442R			5.78		
M50-3150542R			7.15		
M50-3150642R	24.00	10.20	8.30	N/A	1300
M50-3150842R		11.50	11.25		
M50-3151042R			13.40		
M50-3151542R	32.00	14.20	20.10	28.40	1400
M50-3152042R	44.00	20.20	26.10	40.40	
M50-3152242R			28.60	40.40	1300
M50-3152542R			32.45	40.40	



- NOTES:
- PRODUCT IS TAPE AND REELED IN GENERAL ACCORDANCE WITH EIA-481 (ELECTRONIC INDUSTRIES ASSOCIATION).
 - CUMULATIVE TOLERANCE OVER 10 PITCHES = $\pm 0.20\text{mm}$
 - FOR CONNECTOR DETAILS AND SPECIFICATIONS SEE SHEET 4.

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = $\pm 1\text{mm}$
X.X = $\pm 0.25\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:

SEE SHEET 4

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: 1.27mm PITCH DIL SMT VERT
LOW PROFILE SOCKET ASSY
(TAPE & REEL)

DRAWING NUMBER:

M50-315XX42R

SHT
3
OF
4

MSP	10	17.08.17	20750
NAME	ISS.	DATE	C/NOTE
APPROVED: M.PERREN			
CHECKED: M.PLESTED			
DRAWN: R.ADDE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

