


1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN, THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.

③ 0.00254-0.00504 [0.000100-0.000200] MATTE TIN-LEAD ON SOLDER TAIL,
ALL OVER 0.00127 [0.000050] NICKEL.

4 HOUSING: LCP, COLOR-BLACK.
POSTS: PHOSPHOR BRONZE

5 0.00254-0.00504 [.000100-.000200] MATTE TIN ON SOLDER TAIL,
ALL OVER 0.00127 [.000050] NICKEL.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



△	101.19	99.06	39	40	9-146274-0
	[3.984]	[3.900]			
	98.65	96.52	38	39	8-146274-9
	[3.884]	[3.800]			
	96.11	93.98	37	38	8-146274-8
	[3.784]	[3.700]			
	93.57	91.44	36	37	8-146274-7
	[3.684]	[3.600]			
	91.03	88.90	35	36	8-146274-6
	[3.584]	[3.500]			
	88.49	86.36	34	35	8-146274-5
	[3.484]	[3.400]			
	85.95	83.82	33	34	8-146274-4
	[3.384]	[3.300]			
	83.41	81.28	32	33	8-146274-3
	[3.284]	[3.200]			
	80.87	78.74	31	32	8-146274-2
	[3.184]	[3.100]			
	78.33	76.20	30	31	8-146274-1
	[3.084]	[3.000]			
	75.79	73.66	29	30	8-146274-0
	[2.984]	[2.900]			
	73.25	71.12	28	29	7-146274-9
	[2.884]	[2.800]			
	70.71	68.58	27	28	7-146274-8
	[2.784]	[2.700]			
	68.17	66.04	26	27	7-146274-7
	[2.684]	[2.600]			
	65.63	63.5	25	26	7-146274-6
	[2.584]	[2.500]			
	63.09	60.96	24	25	7-146274-5
	[2.484]	[2.400]			
60.55	58.42	23	24	7-146274-4	
[2.384]	[2.300]				
58.01	55.88	22	23	7-146274-3	
[2.284]	[2.200]				
55.47	53.34	21	22	7-146274-2	
[2.184]	[2.100]				
52.93	50.80	20	21	7-146274-1	
[2.084]	[2.000]				
50.39	48.26	19	20	7-146274-0	
[1.984]	[1.900]				
47.85	45.72	18	19	6-146274-9	
[1.884]	[1.800]				
45.31	43.18	17	18	6-146274-8	
[1.784]	[1.700]				
42.77	40.64	16	17	6-146274-7	
[1.684]	[1.600]				
40.23	38.10	15	16	6-146274-6	
[1.584]	[1.500]				
37.69	35.56	14	15	6-146274-5	
[1.484]	[1.400]				
35.15	33.02	13	14	6-146274-4	
[1.384]	[1.300]				
32.61	30.48	12	13	6-146274-3	
[1.284]	[1.200]				
30.07	27.94	11	12	6-146274-2	
[1.184]	[1.100]				
27.53	25.40	10	11	6-146274-1	
[1.084]	[1.000]				
24.99	22.86	9	10	6-146274-0	
[.984]	[.900]				
22.45	20.32	8	9	5-146274-9	
[.884]	[.800]				
19.91	17.78	7	8	5-146274-8	
[.784]	[.700]				
17.37	15.24	6	7	5-146274-7	
[.684]	[.600]				
14.83	12.70	5	6	5-146274-6	
[.584]	[.500]				
12.29	10.16	4	5	5-146274-5	
[.484]	[.400]				
9.75	7.62	3	4	5-146274-4	
[.384]	[.300]				
7.21	5.08	2	3	5-146274-3	
[.284]	[.200]				
4.67	2.54	1	2	5-146274-2	
[.184]	[.100]				
2.13	-	0	1	5-146274-1	
[.084]	[-]				
PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

OBSOLETE 6		[101.19 3.984][3.900]	39	40	4-146274-0	
		[98.65 3.884][3.800]	38	39	3-146274-9	
		[96.11 3.784][3.700]	37	38	3-146274-8	
		[93.57 3.684][3.600]	36	37	3-146274-7	
SUPERCEDED BY 8-146274-6		[91.03 3.584][3.500]	35	36	3-146274-6	
OBSOLETE 6		[88.49 3.484][3.400]	34	35	3-146274-5	
		[85.95 3.384][3.300]	33	34	3-146274-4	
		[83.41 3.284][3.200]	32	33	3-146274-3	
		[80.87 3.184][3.100]	31	32	3-146274-2	
		[78.33 3.084][3.000]	30	31	3-146274-1	
		[75.79 2.984][2.900]	29	30	3-146274-0	
		[73.25 2.884][2.800]	28	29	2-146274-9	
		[70.71 2.784][2.700]	27	28	2-146274-8	
		[68.17 2.684][2.600]	26	27	2-146274-7	
		[65.63 2.584][2.500]	25	26	2-146274-6	
OBSOLETE 6		[63.09 2.484][2.400]	24	25	2-146274-5	
		[60.55 2.384][2.300]	23	24	2-146274-4	
		[58.01 2.284][2.200]	22	23	2-146274-3	
		[55.47 2.184][2.100]	21	22	2-146274-2	
		[52.93 2.084][2.000]	20	21	2-146274-1	
		[50.39 1.984][1.900]	19	20	2-146274-0	
		[47.85 1.884][1.800]	18	19	1-146274-9	
		[45.31 1.784][1.700]	17	18	1-146274-8	
		[42.77 1.684][1.600]	16	17	1-146274-7	
		[40.23 1.584][1.500]	15	16	1-146274-6	
OBSOLETE 6		[37.69 1.484][1.400]	14	15	1-146274-5	
		[35.15 1.384][1.300]	13	14	1-146274-4	
		[32.61 1.284][1.200]	12	13	1-146274-3	
		[30.07 1.184][1.100]	11	12	1-146274-2	
		[27.53 1.084][1.000]	10	11	1-146274-1	
		[24.99 984][.900]	9	10	1-146274-0	
		[22.45 884][.800]	8	9	146274-9	
		[19.91 784][.700]	7	8	146274-8	
		[17.37 684][.600]	6	7	146274-7	
		[14.83 584][.500]	5	6	146274-6	
SUPERCEDED BY 5-146274-5		[12.29 484][.400]	4	5	146274-5	
SUPERCEDED BY 5-146274-4		[9.75 384][.300]	3	4	146274-4	
SUPERCEDED BY 5-146274-3		[7.21 284][.200]	2	3	146274-3	
SUPERCEDED BY 5-146274-2		[4.67 184][.100]	1	2	146274-2	
SUPERCEDED BY 5-146274-1		[2.13 .084][-]	0	1	146274-1	
PLATING		C	B	A	NO. OF POSITIONS	PART NUMBER

RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063 [1.60] THICK PC BOARD AND
.012 [.305] STENCIL THICK.

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN G. HOFFMAN	6/12/95	 TE Connectivity	
		CHK G. DUBNICZKI	6/29/95		
dimensions: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		G. DUBNICZKI APPRO PRODUCT SPEC		HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW, HIGH TEMPERATURE, VERTICAL	
MATERIAL		APPLICATION SPEC		SIZE	CAGE CODE
		WEIGHT		DRAWING NO	RESTRICTED TO
SEE TABLE		—		A1	00779
		CUSTOMER DRAWING		SCALE	4:1
				SHEET	1 of 1
				REV	G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146274-1](#)