


FED. MFG. CODE 91929

CATALOG LISTING

JS-350



FOUR SLOTS EQUALLY
SPACED .080 WIDE X
↓ .040

$\varnothing .875 \pm .010$

-.19±.06


— SWITCH POTTED
AT REAR

2 WIRE LEADS PER
MIL-W-22759/18
24 AWG

.330±.010

5 .19 MIN WITH .090 PANEL THICKNESS AS SHOWN

[illegible]

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.					THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA			SCALE NONE	
ACTUATING FORCE ----- 4±1 LBS		CONTACT ARRANGEMENT SPST NO			DO NOT SCALE PRINT	
RELEASE FORCE ----- 1 LB MIN					UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
TOTAL TRAVEL ----- .085±.015		SEA LEVEL			ONE PLACE (.) ±.030	
TEMP ----- -55°C TO +85°C		LOAD	20 VDC	115 VAC	20 VDC	TWO PLACE (.00) ±.015
		RESISTIVE	10 AMP	10 AMP	----	THREE PLACE (.000) ±.005
		INDUCTIVE	5 AMP	5 AMP	5 AMP	ANGLES ±
		LAMP	3 AMP	3 AMP	----	WEIGHT .050 LBS MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[JS-350](#)