



SHOULDER ELECTRONICS LIMITED

SAW FILTER FOR TELECOMMUNICATION

Part Number	Center Frequency (MHz)	Passband width(MHz)	Insertion Loss(dB) Within Passband	Stopband Attenuation (dB)		I/O Impedance		SAMPLE DIMENSIONS TEST CIRCUIT
				Fo-100i× Fo-40.8	Fo+40.8i× Fo+100	A Type	B Type	
HDFiöiöiöA	402,406,410,414	Fo;À2.0	4.5dB Max	55dB Min	55dB Min	50i, /0pF	150i, /0pF	
	418,422,426,430							
	434,438,442,446							
HDFiöiöiöB	450,454,458,462							
	465,470,474,478							
	482,486,490,494							
	498,502,506,510							
	514,518,522,526							

ii



[\[Home | About SDE | Request Info | Saw Filter | Saw Resonator | Ceramic Resonator | Ceramic Discriminator |](#)
[Ceramic Filter1 | Ceramic Filter2 | Ceramic Trap | Crystal Unit | Clock Oscillator | Dielectric Filter | Dielectric Resonator\]](#)

Copyright 2001 by Shoulder Electronics Limited
 Contact Us: Tel: 86-755-2979884 Fax:86-755-2979885
 Questions or comments: info@china-shoulder.com