





Chicago Miniature Lighting, LLC

Lighting the world since 1910

Neon Indicator Lamps

Neon Indicator Lamps

Configuration	Part Number	Old Ref. Number	Design Current mA	Maximum Breakdown Voltage	
				VAC	VDC
Wire Terminal-Standard Brightness					
	2ML	NE -38S	0.3	65	90
	A1A	NE -2	0.6	65	90
	A1A-T	NE -2T	0.6	65	90
	A1B		0.3	65	90
	A1D		0.3	65	90
	A1D-T		0.3	65	90
	K4A	AR -9	0.3	80	115
	A2B	NE -2V	0.7	65	90
	A2B-T	NE -2VT	0.7	65	90
	A9A	NE -2E	0.7	65	90
	A9A-T	NE -2E T	0.7	65	90
	A9A-C	NE -2E 1	0.7	65	90
A9A-C T	NE -2E 1T	0.7	65	90	
Wire Terminal-High Brightness					
	1MH	NE -38	1.2	95	135
	A1C		1.2	95	135
	A1C-T		1.2	95	135
	G2B-1		1.2	95	135
	G2B-2		1.4	95	135
	A3C	NE -2U	1.9	95	135
	A3C-T	NE -2UT	1.9	95	135
	C2A	NE -2H	1.9	95	135
	C2A-T	NE -2HT	1.9	95	135
	C2A-C	NE -2H 1	1.9	95	135
	D2A		2.6	95	135

Footnotes

- Life value is to approximately 50% of initial light output. Values shown apply to use on AC unless otherwise shown. Life on DC is approximately 60% of AC values when DC current is equal to RMS AC value. When equal DC and RMS AC voltages and equal resistances are utilized, life will be approximately the same.
- For DC operation of high brightness lamps use a minimum of 150 circuit volts. Maximum initial breakdown voltage 95 VAC, 135 VDC in light.
- Tinned leads.
- High brightness.
- Formed tip.
- Dark effect reduced.
- Lamp drops through a Ø.310" cylinder of .500" minimum length.

147 Central Avenue
Hackensack, NJ 07601
Phone: (201) 489-8989
Fax: (201) 489-6911

18703 Dix Toledo Road
Brownstown, MI 48193

Saret Zone Franca, Edificio B
Alajuela Costa Rica

E-mail: sales@chml.com • Web Site: www.chml.com

Chicago Miniature Lighting, LLC reserves the right to make specification revisions that enhance the design and/or performance of the product