


6 mm Square Thin Type SMD Light Touch Switches

Type: **EVQP0**
EVQQ2




■ Features

- External dimensions : 6.5 mm×6.0 mm, Height 1.8 mm (Excluding the push plate)
- With or without ground terminal, height, operating force
- Overstroke travel

■ Recommended Applications

- Operating switches for other electronic equipment
- Operation switches for PC mouse
- Car audio systems

■ Explanation of Part Numbers








■ Specifications

Type			Snap action/Push-on type SPST
Electrical	Rating		10 μA 2 Vdc to 20 mA 15 Vdc (Resistive load)
	Contact Resistance		100 mΩ max.
	Insulation Resistance		100 MΩ min. (at 100 Vdc)
	Dielectric Withstanding Voltage		250 Vac for 1 minute
	Bouncing		10 ms max. (ON, OFF)
Mechanical	Operating Force	EVQP0	0.6 N, 1.0 N
		EVQQ2	0.5 N, 1.0 N, 1.3 N, 1.6 N, 2.6 N, 3.5 N
	Travel		Short push travel 0.25 mm, Overstroke travel 0.35 mm
Endurance	Operating Life	EVQP0	0.6 N : 2000000 cycles min. 1.0 N : 1000000 cycles min.
		EVQQ2	0.5 N : 2000000 cycles min. 1.0 N, 1.3 N, 1.6 N : 1000000 cycles min. 2.6 N : 200000 cycles min. 3.5 N : 100000 cycles min.
Operating Temperature			-20 °C to +70 °C
Storage Temperature			-40 °C to +85 °C (Bulk) -20 °C to +60 °C (Taping)
Minimum Quantity/Packing Unit			H=2.0 mm 4000 pcs. Embossed Taping (Reel Pack) H=2.5 mm, 3.1 mm 2000 pcs. Embossed Taping (Reel Pack)
Quantity/Carton			H=2.0 mm 20000 pcs. H=2.5 mm, 3.1 mm 10000 pcs.



Note: Non washable

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.


■ Dimensions in mm (not to scale)

No. 1					
EVQP0					
Overstroke travel : 0.35 mm With J-bent terminals					
	   Circuit Diagram  PWB land pattern for reference				
Part Numbers	Operating Force	Height	Push Plate Color	Ground Terminal	Operating Life
EVQP0N02B	0.6 N	2.5 mm	Blue	Without	2000000 cycles
EVQP0P02B	0.6 N	2.5 mm	Blue	With	2000000 cycles
EVQP0Q02Q	1.0 N	2.5 mm	Gray	Without	1000000 cycles
EVQP0S02Q	1.0 N	2.5 mm	Gray	With	1000000 cycles


■ Dimensions in mm (not to scale)

No. 2					
EVQQ2					
Short push travel : 0.25 mm With J-bent terminals					
					
					
		Circuit Diagram			
		PWB land pattern for reference			
		Height			
		H			
		2.0±0.2			
		2.5±0.2			
		3.1 ^{+0.3} _{-0.1}			

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping



Unit: mm

Part No.	Height	A	B	W	F	E	P1	P2	P0	D0 Dia	t1	t2
EVQP0, EVQQ2	2.0	6.7±0.2	7.5±0.2	12.0±0.3	5.5±0.1	1.75±0.10	8.0±0.1	2.0±0.1	4.0±0.1	1.5 ^{+0.1} ₋₀	0.30±0.05	2.2±0.2
	2.5/3.1											3.2±0.2


● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	φ380.0±2.0	φ80.0±1.0	φ13.0±0.2	φ21.0±0.8	2.0±0.5

Item	W	T	t	r
Rate (mm)	13.5±1.0	17.5±1.0	—	—

■ Recommended Shape of Test Pole



■ Recommended Operating Conditions

