

Power PCB Relay RT1 bistable

- 1 pole 16A, 1 form C (CO) or 1 form A (NO) contact
- Polarized bistable version with 1 or 2 coils
- 5kV/10mm coil-contact
- **■** Reinforced insulation
- WG version: product in accordance to IEC 60335-1

Typical applications

Battery powered equipment or applications with "memory function"



F0176-C



Ý.	c 711 us	(1)
_		C - U


Approvals
VDE Cert. No. 40007571, UL E214025, cCSAus 1142018
Technical data of approved types on request


Contact Data	
Contact arrangement 1	form C (CO) or 1 form A (NO)
Rated voltage	250VAC
Max. switching voltage	400VAC
Rated current	16A
Limiting continuous current	16A, UL: 20A
Limiting making current, max. 4s, duty fa	actor 10% 30A
Breaking capacity max.	4000VA
Contact material	AgNi 90/10
	AgNi 90/10 gold plated
Frequency of operation, with/without loa	d 360/72000h ⁻¹
Operate/Reset time max.	10/10ms
Bounce time max., form A/form B	3/6ms

Contact ratings

Туре	Contact	Load	Cycles
IEC 61810			
RT314	A (NO)	16A, 250VAC resistive, 85°C	$30x10^{3}$
RT314	C (CO)	16A, 250VAC resistive, 85°C	10x10 ³
UL 508			
RT314	A/B (NO/NC)	20A, 250VAC, general purpose, 85°C	6x10 ³
RT334	A (NO)	16A, 250VAC, general purpose, 85°C	$50x10^3$
RT314	A (NO)	1hp, 240VAC, 40°C	1x10 ³

Mechanical endurance >5x10⁶ operations






Coil Data, bistable coils	1 coil	2 coils
Magnetic system	polariz	ed, bistable
Coil voltage range	3 to	36VDC
Operative range, IEC 61810		2
Limiting voltage, % of rated coil voltage	120%	150%
Min./Max. energization duration	30ms/1min at	t <10% duty factor
Coil insulation system according UL144	16 c	lass F


Coil versions, bistable coil										
Coil	Rated	Set	Reset	Coil	Rated coil					
code	voltage	voltage	voltage	resistance	power					
	VDC	VDC	VDC	$\Omega \pm 10\%$	mW					
bistable	1 coil									
A03	3	2.1	1.7	21	429					
A05	5	3.5	2.8	62	403					
A06	6	4.2	3.3	90	400					
A12	12	8.4	6.6	360	400					
A24	24	16.8	13.2	1440	400					
bistable	2 coils									
F03	3	2.1	1.7	15	600					
F05	5	3.5	2.8	42	595					
F06	6	4.2	3.3	55	655					
F09	9	6.3	5.0	135	600					
F12	12	8.4	6.6	240	600					
F24	24	16.8	13.2	886	650					
F36	36	25.2	19.8	1994	650					

All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request.

Bistable coils - operation

Distable colls - operation				
Version	1 coil		2 coils	
Coil terminals	A1	A2	A1 A3 A2	
Operate	+	-	+ -	
Reset	-	+	- +	
Contact position not defined at delivery				







Power PCB Relay RT1 bistable (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	$1000V_{rms}$
between contact and coil	5000V _{rms}
Clearance/creepage	
between contact and coil	≥ 10/10mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI 250V

0	th	er	D	a	ta

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature -40 to 85°C

Category of environmental protection

IEC 61810 RTII - flux proof, RTIII - wash tight

Vibration/shock resistance (functional),

opening B contact 3/5g opening closed A contact 6/15g Shock resistance (destructive) 100g

PCB-THT, plug-in ¹⁾
14g
T, IEC 60068-2-20
270°C/10s
260°C/5s
tube/20 pcs., box/500 pcs.
, see Accessories.


Accessories

For 1 coil version,

details see datasheet <u>Accessories Industrial Power Relay RT</u>

NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.

Dimensions





- a) Indicated contact position during or after coil energization with reset voltage.
- b) for 2 coil version only

PCB layout / terminal assignment

Bottom view on solder pins


16A, pinning 5mm, 1 form A (NO) contact






*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.

12A, pinning 3,5mm, 1 form A (NO) contact



16A, pinning 5mm, 1 form C (CO) contact



*) With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.



Power PCB Relay RT1 bistable (Continued)

Product code structure				Туріс	ical product code	RT	3	1	4	F24
Туре										
	RT Power PCB Relay RT1 bistable									
Version	1						_			
	1 12A, pinning 3,5mm, flux proof	3	16A, pinning 5mm, flux proof	D	16A, pinning 5r	nm, was	h tight			
Contac	t configuration							-		
	1 1 form C (CO) contact	3	1 form A (NO) contact							
Contac	t material									
	4 AgNi 90/10	5	AgNi 90/10 gold plated							
Coil										
	Coil code: please refer to coil versions ta	ble								

Version

Blank Standard version

WG Product in accordance with IEC 60335-1 (domestic appliances)

Product code	Version	Contacts	Contact material	Coil version	Coil	Part number
RT315A03WG	16A,	1 form C (CO)	AgNi 90/10 gold plated	Bistable 1 coil	3VDC	8-1415545-5
RT314A03	pinning 5mm,	contact	AgNi 90/10		3VDC	7-1393239-7
RT314A05	flux proof				5VDC	7-1393239-8
RT314A06					6VDC	7-1393239-9
RT314A12					12VDC	8-1393239-0
RT314A24WG					24VDC	1415539-5
RT314F03				Bistable 2 coils	3VDC	8-1393239-4
RT314F05					5VDC	8-1393239-5
RT314F06					6VDC	8-1393239-6
RT314F09					9VDC	6-1415351-1
RT314F12					12VDC	8-1393239-7
RT314F24					24VDC	8-1393239-8
RT314F36					36VDC	8-1393239-9
RTD14F03	16A,				3VDC	5-1393238-7
RTD14F12	pinning 5mm,				12VDC	5-1393238-8
RTD15F05	wash tight		AgNi 90/10 gold plated		5VDC	1415538-8
RT134F12	12A,	1 form A (NO)	AgNi 90/10		12VDC	1415544-5
RT134F24	pinning 3,5mm,	contact			24VDC	4-1415382-1
RT114F12	flux proof	1 form C (CO)			12VDC	6-1415543-8
RT114F24		contact			24VDC	5-1415400-1

Other types on request.

This list represents the most common types and does not show all variants covered by this datasheet.