



DRAWING NO. SD206499		1		2		3		4	
CATALOG NUMBER	I.P.S. PIPE ACCOMMODATED			COPPER CABLE ACCOMMODATED		H	J	W	RECOMMENDED TIGHTENING TORQUE
	NOMINAL O.D.	ACTUAL O.D.		AWG	METRIC WIRE SIZE				
		(in)	[mm]						
GAR3902	1/2"-1"	.840-1.32	[22-33]	4 STR(.232)- 4/0 STR(.528)	25mm² STR[6.6]- 95mm² STR[12.9]	3.50 [89]	3/8"-16	3.25 [83]	200 Lb*in [22.5 N*m]
GAR3903	1-1/4"-2"	1.66-2.38	[43-60]			4.00 [102]		4.25 [108]	
GAR3904	2-1/2"-3-1/2"	2.88-4.00	[74-101]			6.50 [165]		6.00 [152]	
GAR3905	4"-5"	4.50-5.56	[115-141]			7.50 [191]		7.50 [191]	
GAR3906	6"	6.62	[168]			8.50 [216]		8.62 [219]	
GAR3907	8"	8.62	[218]			10.00 [254]		10.62 [270]	
GAR3908	10"	10.75	[273]			12.00 [305]		12.75 [324]	
GAR3909	12"	12.75	[323]			14.00 [356]		14.75 [375]	
REV.		DATE		DESCRIPTION		BY		C*K'D.	
2		9-Jun-99		REVISED TIGHTENING TORQUE PER ESD 4861		JRW		PL	



NOTES:

- MATERIAL: AS NOTED.
- UL 467 LISTED, FILE NO. E9999. ACCEPTABLE FOR DIRECT BURIAL.
- CSA C22.2 NO. 65 LISTED, FILE NO. 42862.
- DIMENSIONS IN [] BRACKETS ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

GAR ASSEMBLY			
CAT NO: GAR (TABLE)	SCALE	FULL SIZE	
DRAWN: MP	11/20/90	CHECKED: ATH	11/20/90
DSGN APPVL: KW	11/20/90	MFG APPVL: N/A	
Q.A. APPVL: AL	11/20/90	MKTG APPVL: N/A	
CAD FILE: SD206499-01_2	PH REF: N/A		
FRAMATOME CONNECTORS USA INC.	MDL REF: N/A		
BURNDY ELECTRICAL	PROJECT:		
MANCHESTER, NH 03108	DRAWING NO.		
U. S. A.	SD206499		
1-800-346-4175	REV		
	2		
	SHEET 1 OF 1		