

NOTES:

- 1. © REPRESENTS A CRITICAL DIMENSION. 2. MINIMUM PUSHOUT FORCE 1.0 LB (4.44N) 3. MAXIMUM BREAKOFF VESTIGE: .015[0.38].

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS ANGLES .XX: ±.01 [0.3] .XXX: ±.005 [0.13] .XXXX: ±.0020 [0.051]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING REPRODUCTION USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

SHEET SCALE: 8:1 DESCRIPTION

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

.100 [2.54] C.L. SHUNT ASSEMBLY DWG. NO.

1/31/90 SHEET 1 OF 2

INSULATOR: PBT, UL 94V-0 COLOR: SEE COLOR SPECIFICATION CONTACT: COPPER ALLOY


F:\DWG\MISC\MKTG\SNT-100-XX-X-X-MKT.SLDDRW


DO NOT SCALE DRAWING

SNT-100-XX-X-X

BY: KOLB







-H OPTION (SAME AS FIG 1 EXCEPT AS SHOWN) SNT-100-XX-X-H SHOWN

* PROPRIETARY NOTE *
THIS DOCUMENT CONTAINS COMPIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESS YES RESERVED BY SAMPLE,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNLIVEDINGEED PERSON OR ENTIFY OR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMPLE, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

SHEET SCALE: 6:1

DESCRIPTION:

.100 [2.54] C.L. SHUNT ASSEMBLY

DWG. NO.

SNT-100-XX-X-X

BY: KOLB

1/31/90

SHEET 2 OF 2