

In most applications, a signal booster ([B120-000-SL](#)) should be used with this cable to ensure a signal strong enough for your display. If transmitting a 1920 x 1200 signal, you should use the High Definition version of this cable ([P561-100-HD](#)), in addition to a signal booster. An alternate, more cost-effective solution is to use a Tripp Lite DVI over Cat5 Extender ([B140-101X](#)) in place of a 100 ft. DVI cable and signal booster.

## DVI Single Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 100-ft.

MODEL NUMBER: **P561-100**



### Description

Tripp Lite's 100-ft. DVI Single Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster ([B120-000-SL](#)) will need to be used with this cable to ensure a signal strong enough for your display.

### Features

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster ([B120-000-SL](#)) will need to be used with this cable to ensure a signal strong enough for your display

## Specifications

General Info	
Product Group	DISPLAY & AUDIO CABLES
OVERVIEW	

### Highlights

- For use with Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 1920 x 1200
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

### System Requirements

- DVI monitor and computer

### Package Includes

- 100-ft. DVI Single Link TMDS Cable (DVI-D M/M)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Intended Application	Connecting Peripherals
Cable Type	DVI
Model Type	DVI
<b>INPUT</b>	
Cable Length (ft.)	100
Cable Length (m)	30.48
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332130860
<b>PHYSICAL</b>	
Color	Black
Style	DVI
<b>CONNECTIONS</b>	
Connector A	DVI-D SINGLE LINK (MALE)
Connector B	DVI-D SINGLE LINK (MALE)
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.