



## Features:

- Ten size and six colour variations of thin-walled heatshrink tubing in easy to dispense display cartons.
- Manufactured from cross-linked semi-flexible polyolefin which shrinks uniformly to form a permanent insulating covering.
- Upon recovery, thin wall tube will conform to the shape it is applied over.
- Ideal for low voltage electrical insulation up to 1000V.



Dimensions : Millimetres

## Basic Properties - Thin Walled Heatshrink Tubing

Operating temperature : -40°C to +125°C.  
 Shrink ratio : 2:1.  
 Standard colours : Black, blue, red, yellow and transparent.  
 Other : Flame retardent. Self-extinguishing. Thin dual wall adhesive lining. 3:1 shrink ratio.

## Specifications

Colour	Minimum Inner Ø as Supplied (D)	Maximum Inner Ø Recovered (d)	Wall Thickness Recovered (W)	Length Per Box (M)	Part Number
Black	1.2	0.6	0.45	15	HSB1206BLK
Brown					HSB1206BR
Clear					HSB1206C
Blue					HSB1206BLUE
Green/Yellow					HSB1206GY
Grey					HSB1206GRY
Black	1.6	0.8			HSB1608BLK
Brown					HSB1608BR
Clear					HSB1608C
Blue					HSB1608BLUE
Green/Yellow					HSB1608GY
Grey					HSB1608GRY

Dimensions : Millimetres

## Specifications

Colour	Minimum Inner Ø as Supplied (D)	Maximum Inner Ø Recovered (d)	Wall Thickness Recovered (W)	Length Per Box (M)	Part Number	
Black	2.4	1.2	0.45	15	HSB2412BLK	
Brown					HSB2412BR	
Clear					HSB2412C	
Blue					HSB2412BLUE	
Grey					HSB2412GY	
Green/Yellow					HSB2412GRY	
Black	3.2	1.6			HSB3216BLK	
Brown					HSB3216BR	
Clear					HSB3216C	
Blue					HSB3216BLUE	
Grey					HSB3216GY	
Green/Yellow					HSB3216GRY	
Black	4.8	2.4		10	HSB4824BLK	
Brown					HSB4824BR	
Clear					HSB4824C	
Blue					HSB4824BLUE	
Grey					HSB4824GY	
Green/Yellow					HSB4824GRY	
Black	6.4	3.2			10	HSB7030BLK
Brown						HSB7030BR
Clear						HSB7030C
Blue						HSB7030BLUE
Grey						HSB7030GY
Green/Yellow						HSB7030GRY
Black	9.5	4.7		HSB10050BLK		
Brown				HSB10050BR		
Clear				HSB10050C		
Blue				HSB10050BLUE		
Grey				HSB10050GY		
Green/Yellow				HSB10050GRY		
Black	12.7	6.4		8		HSB13060BLK
Brown						HSB13060BR
Clear						HSB13060C
Blue						HSB13060BLUE
Grey						HSB13060GY
Green/Yellow						HSB13060GRY

Dimensions : Millimetres

## Specifications

Colour	Inner Ø as Supplied D Minimum	Inner Ø Recovered d Maximum	Wall Thickness Recovered W	Length Per Box (M)	Part Number
Black	19.1	9.5	0.7	7	HSB190100BLK
Brown					HSB190100BR
Clear					HSB190100C
Blue					HSB190100BLUE
Grey					HSB190100GY
Green/Yellow					HSB190100GRY
Black	25.4	12.7	0.75	4	HSB260120BLK
Brown					HSB260120BR
Clear					HSB260120C
Blue					HSB260120BLUE
Grey					HSB260120GY
Green/Yellow					HSB260120GRY

Dimensions : Millimetres

**Disclaimer** This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-Power is the registered trademark of the Group. © Premier Farnell plc 2009.