



SPECIFICATIONS

SILIKROME®	GRADE	
	COMMERCIAL	MILITARY
Material	Silicone Rubber ASTM D 1418	Silicone Rubber conforming to A-A-59588 Class II GR 50
Temperature Range	-112°F to +400°F (-80°C to +204°C)	-160°F to +450°F (-106°C to +260°C)
	-112°F to +575°F (-80°C to +302°C)	
Shelf Life	25 Years (minimum)	
Resistant to	Salt spray, sunlight, ozone, cleaning solutions, and most acids	
Physical Characteristics	Flexible, non-breakable, re-usable. Acts as shock mount. Protects against shattering. Easy to mount.	



SECTION AA

C	REDRAWN and MAT'L CHANGED	S. GOK	05.28.09
B	CAD COMPUTER GENERATED		01.10.03
A	ADDED 15° - 11/16 WAS 5/8		01.06.64
REV.	DESCRIPTION		DATE
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.	SILIKROMES® COLORED FILTERS FOR INCANDESCENT T-1 3/4 LAMPS	ENG. S. GOK	05.28.09
		DWN. ED	01.22.63
		CHKD. J. CELLA	05.28.09
MAT'L: SEE ABOVE	APM-HEXSEAL CORPORATION	SCALE 4 : 1	1813/8
COLOR: SPECIFY		DWG. NO.	

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

APM HEXSEAL:

[1813/8](#) [1813/8 A2 C](#) [1813/8 B1 C](#) [1813/8 G1 C](#) [1813/8 LW1 C](#) [1813/8 R1 C](#) [1813/8 Y1 C](#) [1813/8 LW1](#)