



Series 121 Tubular Solenoid



GENERAL DESCRIPTION

● DC operated



● Noise reduction feature

● Tubular solenoid

PERFORMANCE


Electrical	ITEM	SPECIFICATION
	Closed power (continuous ratings)	7.0W
	Maximum permissible voltage	160V DC
	Dielectric strength	1KV RMS 50Hz
Mechanical	Insulation	1KV
	Weight	Total: 82g Plunger: 20g
	Ambient temperature	The information given on this page is based on a working temperature of 20°C.
	Force/stroke curve	This force stroke curve shows average performance only with coil at ambient temperature. In addition to normal manufacturing tolerances, deviations can be expected at some voltages due to the coil winding tolerances.

FORCE/STROKE CURVE AND RESPONSE TIME




DIMENSIONS (mm)

Push type - shown energised



Pull type - shown energised

Thread: 0.562" - 18 UNF



Leads: 24 AWG UL1430
Length: 152.0 minimum

COIL DATA

Pull Type	Push Type	Resistance (20°C) Ω ±10%	Cont. (100%) Vdc	50% Vdc	25% Vdc	10% Vdc
121 420 610 540	121 420 620 540	5.14	6	8.5	12	19
121 420 610 620	121 420 620 620	20.6	12	17	24	38
121 420 610 720	121 420 620 720	82.3	24	34	48	76
Watts at 20°C			7	14	28	70
Max. on time (Secs)			∞	230	25	6

Other voltages available on request

Duty cycle (%) =

“ON” time

“ON” time + “OFF” time

x 100%

