

NUMBER OF POSITIONS	DIMENSION	
	A	B
08	7.62	14.86
10	10.16	17.40
12	12.70	19.94
14	15.24	22.48
16	17.78	25.02
18	20.32	27.56
20	22.86	30.10
22	25.40	32.64
24	27.94	35.18
26	30.48	37.72
30	35.56	42.80
34	40.64	47.88
36	43.18	50.42
40	48.26	55.50
44	53.34	60.58
50	60.96	68.20
60	73.66	80.90
64	78.74	85.98

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: Nickel 50μ"

Contact Material: Brass

Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.












Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C

RoHS


REV.	DESCRIPTION	DATE
A	RELEASE	2012/11/7



8P

10P-12P

14P-64P



Mating Part Number		
3020-ALL	3010-XX-001-11-XX	3010-XX-001-13-XX
3010-XX-002-13-XX	3010-XX-003-13-XX	

UNLESS TOLERANCE		DRAW BY	CnC Tech,LLC		
GENERAL	ANGLE	DESIGN BY			
X. ± 0.30	X." ± 3.0"	CHECK BY			
.X ± 0.25	.X" ± 2.0"	APPROVE BY			
.XX ± 0.20	.XX" ± 1.0"		Part NO.		
.XXX ± 0.10	.XXX" ± 0.5"		3030-XX-0104-99		
SCALE		SHEET	UNIT	DRW NO:	
1:1		1/1	MM	REV: A	