



REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED	8/20/99
A	WIRE DIAGRAM CHNGS	10/31/00
B	CONVERT TO CAD	6/8/01
C	ADD HOLE DIA.	3/15/02





CHARACTERISTICS	MIN	TYP	MAX
INPUT VOLTAGE: (vdc)	2.5	3.0	3.5
INPUT CURRENT: (mA)	350	400	450
OUTPUT VOLTAGE: (Vrms)	600	650	700
OUTPUT CURRENT (maRms)	4.0	4.5	5.0
OUTPUT FREQUENCY: (kHz)	70	80	90
OPERATING TEMP: (CELSIUS)	0	25	50



BOARD PIN #	INPUT
1	+V (V in)
2	V (GND)
3	OUT GND
4	V OUT

TOLERANCE	
$L < 20$	± 0.2
$20 \leq L < 50$	± 0.3
$50 \leq L < 100$	± 0.4
$100 \leq L$	± 0.5



METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION TITLE 3 V CCFL POWER SUPPLY			
	TOLERANCE UNLESS OTHERWISE SPECIFIED					
		1 PL +/- 0.2				
		2 PL +/-				
		ANGLE +/- 0				
DRAWN BY	APP'VD BY	DATE	SIZE	FSCM NO.	DRAWING	
L. WENGSTROM	F.D.	3/15/02	A	55335	NO.	BXA-302
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	RELEASED	REVISION	REV.
				DATE	DATE	NO.
			NONE	8/20/99	3/15/02	C