




8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REV

DATE

BY

APP'D

AD

00

1

24JAN05

24JAN05

24JAN05

DESCRIPTION

DATE

DWN

APP'D

—

—

—

—

1

MATERIAL:

CONTACT: PHOSPHOR BRONZE.

HOUSING: GLASS-FILLED POLYESTER.

2

GENERAL PLATING SPECIFICATION: UNDERPLATING

(ENTIRE CONTACT): 1.27μm MIN NICKEL AND ACTION

PIN: 0.5μm MIN TIN.

FOR PLATING OF MATING SURFACES SEE APPLICABLE

SPECIFICATION REFERENCE FOR EACH DASH NUMBER.

3

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101

PERFORMANCE LEVEL 2.

4

CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101

PERFORMANCE LEVEL 1.

5

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,

CENTRAL OFFICE APPLICATIONS.

6

CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL 3,

UNCONTROLLED ENVIROMENT APPLICATIONS.

7

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.

ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,

MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.

8

PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID

PATTERN DEFINED BY CONTACT LAYOUT.

9

FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".

10

FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".

11

TO BE MEASURED AT BOTTOM OF SHROUD.

12

POLARIZATION FEATURE.

13

AREA RESERVED FOR KEYING PART (BASIC P/N 100525).

14

CONNECTOR LUBRICATED WITH BELCORE APPROVED LUBRICANT,

TECHNICAL REFERENCE: TR-NWT-001217 ISSUE 1, SEP 1992.

15

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
B CARBO
CHK
G SKIPPER
APP'D
G SKIPPER
PRODUCT SPEC

24JAN05
24JAN05
24JAN05

NAME
MALE ASSEMBLY, Z-PACK 2mm HM,
TYPE A

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0-PLG ±
1-PLG ± 0.1
2-PLG ±
3-PLG ±
4-PLG ±
ANGLES

±0.2

MATERIAL
SEE SHEET 1

FINISH
SEE SHEET 1

WEIGHT
—

SIZE
A1

CAGE CODE
00779

DRAWING NO
5100668

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
D1

4805 (3/11)