


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		E	PER EC 0S14-0184-04	12JAN05	BM	JL



-  PHOSPHOR BRONZE PER QQ-B-750.
-  BRASS PER QQ-B-626.
-  ZINC PER QQ-Z-363.
-  POLYESTER, PBT, PER MIL-M-24519.
-  TIN PLATE PER ASTM-B-545
2.54 μm [.000100] MINIMUM THICK.
-  NICKEL PLATE PER QQ-N-290
3.81 μm [.000150] MINIMUM THICK.
-  GOLD PLATE PER MIL-G-45204,
0.76 μm [.000030] MINIMUM THICK.
- 8. SEE INSTRUCTION SHEET 408-9889.

DRILL HOLE TO RECEIVE
0.94±0.06 [.037±.002]
DIA PIN, 5 REQUIRED

SUGGESTED PCB CONFIGURATION

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. LIPPERT 10-16-92		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK A. GABANY 10-22-92		NAME JACK, 50 OHM, VERTICAL, PCB, BNC —						
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.20 [.008] 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD A. GABANY 10-22-92		PRODUCT SPEC 108-12078							
	MATERIAL		APPLICATION SPEC		SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO	
	SEE NOTES 1 — 4		FINISH		WEIGHT —				A2 00779 C=414460		—	
CUSTOMER DRAWING					SCALE 5:1		SHEET 1 OF 1		REV E			