


COMPONENTS		MATERIAL					
BODY		BRASS PER ASTM-B16				IMPEDANCE _____ 75 OHMS	
INSULATORS		TEFLON PER ASTM-D1710, REXOLITE PER Q 200.5, DELRIN PER ASTM D 4181				VOLTAGE RATING _____ 500 VRMS	
CONTACTS		BERYLLIUM COPPER PER ASTM-B196				INSULATION RESISTANCE _____ 5,000 MEGOHMS	
						FREQUENCY RANGE _____ DC-2 GHz	
						VSWR _____ 1.4 MAX TO 2 GHz	

DASH	FINISH		INSULATOR	DIM A	DIM B
	BODY	CONTACT			
-1	NICKEL	GOLD	TEFLON	.78	.25
-2	NICKEL	GOLD	TEFLON	.94	.38
-3	NICKEL	GOLD	REXOLITE	.94	.38
-4	NICKEL	GOLD	DELRIN	.94	.38



SALES DRAWING

APPROVED T.L. BROWNING 7/10/98	A	TOLERANCES (EXCEPT AS NOTED) DIM. .XX ±.020 .XXX ±.005 ANGLES ±1° CONC. .005 TIR SURF. 64 √ FSCM NO. 24931	DRAWN BY: B THOMMEN	DATE: 8-28-92	TITLE: 'F' SERIES
			SCALE:	CAD FILE: N/A	JACK TO JACK
			BERG ELECTRONICS RF/COAXIAL DIVISION 2100 EARLYWOOD DRIVE FRANKLIN, INDIANA 46131		ADAPTER
			PART NO. 33A116		SHT. 1 OF 1