




DATA SHEET

Part Number: SL15 5R009-03

Ordering Different Lead Types:

Inside Kinked Leads	Use -A after Ametherm's part #
Outside Kinked Leads	Use -B after Ametherm's part #

For example: to order an inside kinked lead use part number SL15 5R009-03-A



Electrical Specifications:

Resistance @ 25°C	5.0 Ω $\pm$ 20%
Max Steady State Current Up to 65°C	9.0 A
Max Recommended Energy Rating (Joules)	50.0 J
Actual Failure Point of Instantaneous Energy (Joules)	75.0 J
Resistance @ 100% of Max Current	0.067 Ω
Resistance @ 50% of Max Current	0.162 Ω
Body Temperature @ 100% Current Rating	200 °C
Dissipation Constant	23mW/°C
Thermal Time Constant	54 seconds
Material Type	"C"
Max Recommended Voltage	265 VAC
Max Recommended Capacitance @ 120VAC/240VAC	3400 μ F/750 μ F

Mechanical Specifications:

D	15.0 $\pm$ 1.0 mm
T	5.0 $\pm$ 0.2 mm
Lead Diameter	1.0 $\pm$ 0.05 mm
S	7.8 $\pm$ 2.0 mm
L	38.0 $\pm$ 9.0 mm
Straight Leads Coating Run Down	5.1 $\pm$ 0.5 mm
B	7.50 $\pm$ 0.70 mm
C	3.82 $\pm$ 1.0 mm
Coating Run Down on the Straight Leads	5.00 $\pm$ 0.5 mm

CSA File Number: #CA118061

Revision Date: July 8, 2003

Ametherm, Inc. 3111 N. Deer Run Road #4 Carson City, NV 89701

Telephone: (800) 808-2434 (775) 884-2434 Fax: (775) 884-0670

www.ametherm.com