

## Housing - DFK-PC 6-16/ 2-GFU-SH-10,16 - 1702015

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Header, Nominal current: 76 A, Rated voltage (III/2): 1000 V, Number of positions: 2, Pitch: 10.16 mm, Color: green, Contact surface: Silver, Mounting: Wave soldering



The figure shows a 5-pos. version of the product

### Product Features

- Well-known mounting principle allows worldwide use
- Flange system enables secure fixing to the housing panel by means of tool-free snap-in locking or screws
- Shroud for professional EMC shield feed-through on the inside of the device
- Screwable flange for superior mechanical stability



### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 10 pc    |
| Weight per Piece (excluding packing) | 22.14 g  |
| Custom tariff number                 | 85366990 |
| Country of origin                    | Poland   |

### Technical data

#### Dimensions

|                          |              |
|--------------------------|--------------|
| Length                   | 34 mm        |
| Pitch                    | 10.16 mm     |
| Dimension a              | 10.16 mm     |
| Constructional height    | 19 mm        |
| Length of the solder pin | 4.1 mm       |
| Pin dimensions           | 1,0 x 1,2 mm |
| Pin spacing              | 10.16 mm     |

# Housing - DFK-PC 6-16/ 2-GFU-SH-10,16 - 1702015

## Technical data

### Dimensions

|               |        |
|---------------|--------|
| Hole diameter | 1.7 mm |
|---------------|--------|

### General

|                                        |                        |
|----------------------------------------|------------------------|
| Range of articles                      | DFK-PC 6-16/...-GFU-SH |
| Insulating material group              | I                      |
| Rated surge voltage (III/3)            | 8 kV                   |
| Rated surge voltage (III/2)            | 8 kV                   |
| Rated surge voltage (II/2)             | 6 kV                   |
| Rated voltage (III/3)                  | 1000 V                 |
| Rated voltage (III/2)                  | 1000 V                 |
| Rated voltage (II/2)                   | 1000 V                 |
| Connection in acc. with standard       | EN-VDE                 |
| Nominal current $I_N$                  | 76 A                   |
| Maximum load current                   | 76 A                   |
| Insulating material                    | PA                     |
| Flammability rating according to UL 94 | V0                     |
| Color                                  | green                  |
| Number of positions                    | 2                      |

### Standards and Regulations

|                                        |        |
|----------------------------------------|--------|
| Connection in acc. with standard       | EN-VDE |
|                                        | CUL    |
| Flammability rating according to UL 94 | V0     |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27141190 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |
| eCl@ss 9.0 | 27440402 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
|----------|----------|

## Housing - DFK-PC 6-16/ 2-GFU-SH-10,16 - 1702015

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

#### Approvals

UL Recognized / SEV / cUL Recognized / EAC / IECEE CB Scheme / EAC / cULus Recognized

#### Ex Approvals

#### Approvals submitted

### Approval details

|                                                                                                   |       |       |       |
|---------------------------------------------------------------------------------------------------|-------|-------|-------|
| UL Recognized  |       |       |       |
|                                                                                                   | B     | C     | D     |
| Nominal current I <sub>N</sub>                                                                    | 66 A  | 66 A  | 5 A   |
| Nominal voltage U <sub>N</sub>                                                                    | 300 V | 300 V | 600 V |

|                                |        |
|--------------------------------|--------|
| SEV                            |        |
| Nominal current I <sub>N</sub> | 76 A   |
| Nominal voltage U <sub>N</sub> | 1000 V |

# Housing - DFK-PC 6-16/ 2-GFU-SH-10,16 - 1702015

## Approvals

| cUL Recognized  |       |       |       |
|--------------------------------------------------------------------------------------------------|-------|-------|-------|
|                                                                                                  | B     | C     | D     |
| Nominal current I <sub>N</sub>                                                                   | 66 A  | 66 A  | 5 A   |
| Nominal voltage U <sub>N</sub>                                                                   | 300 V | 300 V | 600 V |

|     |
|-----|
| EAC |
|-----|


| IECEE CB Scheme  |        |
|---------------------------------------------------------------------------------------------------|--------|
|                                                                                                   |        |
| Nominal current I <sub>N</sub>                                                                    | 76 A   |
| Nominal voltage U <sub>N</sub>                                                                    | 1000 V |

|     |
|-----|
| EAC |
|-----|


|                                                                                                      |
|------------------------------------------------------------------------------------------------------|
| cULus Recognized  |
|------------------------------------------------------------------------------------------------------|

## Drawings

Drilling diagram




Dimensional drawing




## Housing - DFK-PC 6-16/ 2-GFU-SH-10,16 - 1702015

Dimensional drawing




Sheet metal cutout for snap-on.

Dimensional drawing



Sheet metal cutout for screw connection.

Diagram



The illustration shows the derating curve for plugs DFK-PC(V) 6-16/...-G(F)(U)-(SH)-10,16 in combination with header PC 16/...-ST(F)-(SH)-10,16.