

## Contact insert - RC-09P1N220000 - 1606999

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)



Contact insert, number of positions: 8+1, type of contact: Pin, Solder-in connection

The figure shows the 6-pos. product version

**RoHS**

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 276153
GTIN	4046356276153
Weight per Piece (excluding packing)	6.510 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Insertion/withdrawal cycles mechanical	50
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Solder-in connection
Type of contacts	Pin
Number of positions	9
Contact diameter of power contacts	2 mm
Rated current for power contacts	20 A
Contact diameter of signal contacts	1 mm
Nominal current per signal contact	8 A

## Contact insert - RC-09P1N220000 - 1606999

### Technical data

#### Material

Insulator material	PBT
Contact material	CuZn
Contact surface	Nickel-plated, gold coating

#### Specifications according to DIN EN 61984:2001

Nominal / operating voltage of power contacts	300 V
Rated surge voltage of power contacts	2.5 kV
Overshoot category of power contacts	II
Degree of pollution of power contacts	3
Nominal / operating voltage of signal contacts	300 V
Overshoot category of signal contacts	II
Degree of pollution of signal contacts	3


#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings


## Contact insert - RC-09P1N220000 - 1606999

Schematic diagram




## Contact insert - RC-09P1N220000 - 1606999

Drilling diagram



## Contact insert - RC-09P1N220000 - 1606999

Dimensional drawing



### Classifications

eCl@ss

eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440205
eCl@ss 8.0	27440205
eCl@ss 9.0	27440205

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121

## Contact insert - RC-09P1N220000 - 1606999

### Classifications

#### ETIM

ETIM 5.0	EC000438
ETIM 6.0	EC000438
ETIM 7.0	EC000438

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121522
UNSPSC 18.0	39121522
UNSPSC 19.0	39121522
UNSPSC 20.0	39121522
UNSPSC 21.0	39121522

### Approvals

#### Approvals

---

Approvals

EAC

---

Ex Approvals

---

#### Approval details

EAC		B.01687
-----	---	---------