

DO NOT
SCALE FROM
THIS PRINT






TABLE 1	
NO OF POS	COPLANARITY
-020 THRU -080	.004 [0.10]
-090 THRU -120	.006 [0.15]

NOTES:

1. \odot REPRESENTS A CRITICAL DIMENSION.
2. NOTE DELETED.
3. MAXIMUM BURR ALLOWANCE: .0015 [.038].
4. MINIMUM PUSHOUT FORCE: .5 LB.
5. NOTE DELETED.
6. -L PLATING MAY BE SUBSTITUTED FOR -F PLATING.
7. MAX VARIENCE: .002 [.05].
8. NOTE DELETED.
9. -90 THROUGH -120 POSITION PARTS USE C-269-11-X. DO NOT SUB C-126-XX-X OR C-224-01-X.
10. POSITIONS 20, 40, 60, 80, 120 ARE TRAY PACKAGED.

PACKAGING VIEW
90 & 100 POS ONLY

TUBE: PT-1-24-03-78
PLUG: TP-09

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: $\pm .01$ [.25] 2°
.XXX: $\pm .005$ [.13] $\pm .002$ [0.051]

* PROPRIETARY NOTE *
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: BLACK LCP
FLAMMABILITY RATING: UL94VO
SOCKET: PHOS BRONZE

SHEET SCALE: 1:51

DESCRIPTION: .8mm DOUBLE ROW SOCKET ASSEMBLY

DWG. NO. BSE-XXX-01-X-D-XX

BY: DEAN P 05/24/1999 SHEET 1 OF 1

Samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 5532

FIG 2
-FL OPTION
BSE-020-01-X-D-A-FL SHOWN
(SAME AS FIG 1, UNLESS OTHERWISE STATED)