

1. Insulation block, POM, yellow
2. Insulator, PBT + 15% glass fiber, white
3. Shell, C3604 brass, 2 μ m nickel plated
4. Spring contact, C5191 phosphor bronze, 2 μ m nickel plated

Dielectric strength: 1 min @ 500 Vac
Insulation resistance: 100 MΩ @ 500 Vdc
Contact resistance: 30 mΩ or less
Rated voltage: 20 Vdc
Rated current: 4 A


Insertion force: 0.5-2 kgf
Withdrawal force: 0.3-1.5 kgf
Durability: 5000 mating cycles while maintaining; 0.4-2 kgf insertion force, 0.2-1.5 kgf withdrawal force and a less than 100 mQ contact resistance.

Damp test: 40 °C, RH 90-100% for 96 hrs. Cool to ambient and recover for 2 hours. Maintain dielectric strength of 500 Vac for 1 min, insulation resistance of 50 MΩ @ 500 Vdc minimum and a contact resistance of 100 mΩ or less.

Dry test: 70 °C, RH 70-85% for 96 hrs. Cool to ambient and recover for 2 hours. Maintain insulation resistance of 50 MΩ @ 500 Vdc minimum and a contact resistance of 100 mΩ or less.

Salt spray test: 35 °C, RH 90-95%, 5% NaCl mist for 24 hrs.
Wash parts after test. Maintain mechanical requirements
and a contact resistance of less than 80 mΩ.

-25 to 70 °C, relative humidity of 85% or less



Revision	Date	Description	Notes		TENSILITY 20802 Sockeye Place #130 Bend, OR 97701 USA tel 541.323.3228 fax 541.323.4202 800 877.670.7118 www.tensility.com			
A	11/7/2012	Initial release	RoHS compliant					
			Function test: no open, no short circuit, no INT					
			DIMENSIONS ARE IN MILLIMETERS	DESCRIPTION:	SIZE	Part number		
			TOLERANCES: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Connector, dc plug, 3.5x1.35xL20mm, brass, nickel plated, molding type, white insulators	A	50-00315		
					SCALE: 2:1	WEIGHT:	SHEET 1 OF 1	