






# +VDC HMC-C010 RFOUT

#### **Typical Applications**

The HMC-C010 is ideal for:

- Fiber Optics
- Military
- Test Equipment

#### **Functional Diagram**



#### **Features**

Wide Bandwidth: 6 - 15 GHz

>600° Phase Shift

Single Positive Voltage Control

Hermetically Sealed Module

Field Replaceable SMA Connectors

-55 to +85 °C Operating Temperature

#### **General Description**

The HMC-C010 is an Analog Phase Shifter which is controlled via an analog control voltage from 0 to +5V. The HMC-C010 provides a continuously variable phase shift of 0 to 800 degrees at 6 GHz, and 0 to 450 degrees at 16 GHz, with consistent insertion loss versus phase shift. The phase shift is monotonic with respect to control voltage. The control port has a modulation bandwidth of 50 MHz. The low insertion loss and extremely robust packaging enable this part to be used in a wide range of applications including the phase adjustment of clocks in fiber optic systems and test equipment. The HMC-C010 is housed in a miniature hermetic module with replaceable SMA connectors.

## Electrical Specifications, $T_A = +25^{\circ} \text{ C}$ , 50 Ohm System

Parameter	Frequency (GHz)	Min.	Тур.	Max.	Units
Phase Shift Range:	6 - 10 GHz 10 - 15 GHz	600 360	800 600		degrees degrees
Insertion Loss	6 - 15 GHz		7	10	dB
Return Loss (Input and Output)	6 - 15 GHz		7		dB
Control Voltage Range	6 - 15 GHz		0 - 5		Volt
Modulation Bandwidth	6 - 15 GHz		50		MHz
Phase Voltage Sensitivity	6 - 15 GHz		120		deg /Volt
Insertion Phase Temperature Sensitivity	6 - 15 GHz		0.5		deg /°C

# **HMC-C010\* PRODUCT PAGE QUICK LINKS**

Last Content Update: 02/23/2017

# COMPARABLE PARTS 🖵

View a parametric search of comparable parts.

## **DOCUMENTATION**

#### **Data Sheet**

• HMC-C010 Data Sheet

# TOOLS AND SIMULATIONS 🖳

• HMC-C010 S-Parameter

#### DESIGN RESOURCES 🖳

- HMC-C010 Material Declaration
- PCN-PDN Information
- · Quality And Reliability
- Symbols and Footprints

# **DISCUSSIONS**

View all HMC-C010 EngineerZone Discussions.

## SAMPLE AND BUY 🖵

Visit the product page to see pricing options.

## TECHNICAL SUPPORT 🖳

Submit a technical question or find your regional support number.

# **DOCUMENT FEEDBACK**

Submit feedback for this data sheet.


This page is dynamically generated by Analog Devices, Inc., and inserted into this data sheet. A dynamic change to the content on this page will not trigger a change to either the revision number or the content of the product data sheet. This dynamic page may be frequently modified.






# 600° ANALOG PHASE SHIFTER MODULE, 6 - 15 GHz


#### Insertion Loss vs. Control Voltage




#### Phase Shift vs. Control Voltage




# Phase Shift vs. Frequency @ Vctl = 5V (Relative to Vctl = 0V)




#### Insertion Loss vs. Frequency



#### Input Return Loss vs. Frequency, Vctl = 0 to +5V



# Output Return Loss vs. Frequency, Vctl = 0 to +5V









# 600° ANALOG PHASE SHIFTER MODULE, 6 - 15 GHz


#### Second Harmonics vs. Control Voltage, Pin = -10 dBm




#### Input IP3 vs. Control Voltage




#### Insertion Loss vs. Pin @ 7 GHz




#### Insertion Loss vs. Pin @ 11 GHz



#### Insertion Loss vs. Pin @ 15 GHz



#### Phase Shift vs. Pin @ 7 GHz









# 600° ANALOG PHASE SHIFTER MODULE, 6 - 15 GHz

#### Phase Shift vs. Pin @ 11 GHz



#### Phase Shift vs. Pin @ 15 GHz



## **Absolute Maximum Ratings**


Control Voltage (Vctl)	-1 Vdc to +8 Vdc	
Input Power (RFIN)	+25 dBm	
Channel Temperature (Tc)	150 °C	
Continuous Pdiss (T = 85 °C) (derate 21 mW/°C above 85 °C)	1.36 W	
Thermal Resistance (junction to ground paddle)	48 °C/W	
Storage Temperature	-65 to +150 °C	
Operating Temperature	-55 to +85 °C	
ESD Sensitivity (HBM)	Class 1B	





# 600° ANALOG PHASE SHIFTER MODULE, 6 - 15 GHz

#### **Outline Drawing**



#### Package Information

Package Type	C-1	
Package Weight [1]	10.2 gms [2]	
Spacer Weight	N/A	

[1] Includes the connectors

[2] ±1 gms Tolerance

#### NOTES:

- 1. PACKAGE, LEADS, COVER MATERIAL: KOVAR™
- 2. BRACKET MATERIAL: ALUMINUM
- 3. PLATING: ELECTROLYTIC GOLD 50 MICROINCHES MIN., OVER ELECTROLYTIC NICKEL 75 MICROINCHES MIN.
- 4. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
- 5. TOLERANCES ±.005 [0.13] UNLESS OTHERWISE SPECIFIED.
- 6. FIELD REPLACEABLE SMA CONNECTORS. TENSOLITE 5602 5CCSF OR EQUIVALENT.
- ↑TO MOUNT MODULE TO SYSTEM PLATFORM REPLACE 0 -80 HARDWARE WITH DESIRED MOUNTING SCREWS.





# 600° ANALOG PHASE SHIFTER MODULE, 6 - 15 GHz

#### **Pin Descriptions**

Pin Number	Function	Description	Interface Schematic	
1	RFIN & RF Ground	RF input connector, SMA female, field replaceable. This pin is DC blocked and matched to 50 Ohms.	RFINO— —	
2	RFOUT & RF Ground	RF output connector, SMA female, field replaceable. This pin is DC blocked and matched to 50 Ohms.	→ ├─○ RFOUT	
3	Vctl	Phase shift control pin. Application of a voltage between 0 and 5 volts causes the transmission phase to change. The DC equivalent circuit is a series connected diode and resistor.	0Vctl 10pF = 80Ω = 11pF = 33pF	
	GND	Power supply ground.	Ç GND =	