

4

3

2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG. 2001


© COPYRIGHT 2001

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
GW	00

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	EC SR10 - 0112 - 04	22DEC2004	RLU	DB



X
16:1



MATED BETWEEN BOARDS



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±0.2
1 PLC	±0.2
2 PLC	±0.1
3 PLC	±
4 PLC	±
ANGLES	±2°
MATERIAL	FINISH
-	-

DWN	S. Kempter	22JUL02
CHK	B. Rithener	22JUL02
APVD	-	-
PRODUCT SPEC	108-71060	-
APPLICATION SPEC	-	-
WEIGHT	-	-
CUSTOMER DRAWING	SCALE	8:1

tyco		Tyco Electronics	
Electronics		Oostkamp - Belgium	
NAME			
BOARD-TO-BOARD CONNECTOR 14 MM HEIGHT -			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-619127	-
SCALE		SHEET	REV
8.1		1 OF 3	A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG. 2001

© COPYRIGHT 2001

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
GWDIST
00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	see sheet 1	-	-	-

1 POSITION OF CENTER CONTACT

2 PLATING 0.15 μm Au OVER NiP3 PLATING 0.3 μm Au OVER NiP,

4 1 CONNECTOR PACKED IN PLASTIC BAG




5 DISTANCE BETWEEN PRINTED CIRCUIT BOARDS

6 MISALIGNMENT BETWEEN CONNECTOR AXIS AND
TARGET LAYOUT ON TARGET BOARD: MAX 0.8 mm

7 ANGLE BETWEEN PRINTED CIRCUIT BOARDS

8 RECOMMENDED LAYOUT ON BASE BOARD

9 RECOMMENDED TARGET LAYOUT ON TARGET BOARD



1	1	5	DIELECTRIC	PCT / PEEK	
1	1	4	OUTER SHELL	CuZn	2
1	1	3	SPRING	STAINLESS STEEL	
1	1	2	CONTACT RING	CuSn	2
1	1	1	CENTER CONTACT ASSEMBLY	CuZn, STAINLESS STEEL	2 3
5--1	-1	ITEM	DESCRIPTION	MATERIAL	PLATING
10 ORDER N°	4 ORDER N°				

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. Kempter 22JUL02	tyco Tyco Electronics Oostkamp - Belgium		
DIMENSIONS: mm		CHK B. Rithener 22JUL02			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME BOARD-TO-BOARD CONNECTOR 14 MM HEIGHT		
0 PLC ± 0.05 1 PLC ± 0.05 2 PLC ± 0.05 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 2^\circ$		PRODUCT SPEC 108-71060	SIZE A3		
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779		
FINISH -		WEIGHT -	DRAWING NO C-619127		
		CUSTOMER DRAWING	RESTRICTED TO -		
			SCALE 8:1		
			SHEET 2 OF 3		
			REV A2		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG. 2001





© COPYRIGHT 2001

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
GWDIST
00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	see sheet 1	-	-	-

B-B
1:1NOZZLE DETAIL
8:1NOZZLE DETAIL
3:1

- 10 PACKAGING:
 -216 CONNECTORS PER TRAY
 -10 TRAYS PER SHIPPING BOX
 -SHIPPING BOX DIMENSIONS (LxBxH): 287x187x200

- 11 ANTISTATIC MATERIAL

- 12 - ALTERNATIVE PACKAGING IN TAPE AND REEL

- 13 CONTACT FORCE FOR CENTER CONDUCTOR:
 F MAX. = 2.8 N (Total length compressed at 13 mm)

- 14 CONTACT FORCE FOR CONTACT RING:
 F MAX. = 5.3 N (Total length compressed at 13 mm)

- 15 RECOMMENDED PCB CHARACTERISTICS :
 - PLATING Au, SURFACE ROUGHNESS Rz4 MAX.
 - PCB MATERIAL FR4
 - PCB THICKNESS MIN. 0.8 mm

- 16 RECOMMENDED NOZZLE DESIGN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
	0 PLC	±0.05	
	1 PLC	±0.05	
	2 PLC	±0.05	
	3 PLC	±	
	4 PLC	±	
MATERIAL		FINISH	

DWN	S. Kempter	22JUL02
CHK	B. Rithener	22JUL02
APVD	-	-
PRODUCT SPEC		
108-71060		
APPLICATION SPEC		
-		
WEIGHT	-	
CUSTOMER DRAWING		

tyco
ElectronicsTyco Electronics
Oostkamp - Belgium

NAME			
BOARD-TO-BOARD CONNECTOR 14 MM HEIGHT			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-619127	-
SCALE		SHEET 3 OF 3	REV A2