





mat'l. code				surface ISO 1302		☒ tolerance ISO 406 ISO 1101		projection 		product family HEADER			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
B	V60842	EPK	6/3/96	angles	linear	.XX±.01/XX±0.3			INCH/MM 	CLINCHER™ LATCH HEADER RIGHT ANGLE			
C	C71289	HTB	9/22/97			.XXX±.005/XX±0.13							
D	M05-0109	MHT	7/15/05	0°±2°		.XXX±.0020/XXX±0.05			scale 4:1	dwg no 95736 sheet 1 of 2 size A3			
E	M06-0052	MHT	1/30/06	dr	T.BREWBAKER 5/23/95								
F	M06-0233	AGS	6/13/06	engr	T. HANNA 5/23/95								
G	M06-0469	MHT	11/28/06	chr	T. HANNA 5/23/95								
H	M09-0059	MHT	4/16/09	appd	T. HANNA 7/6/95								
sheet index	revision sheet	H	H										
		1	2										

PRODUCT NO. NOTE 5	NO. OF POSITIONS	DIM K ENGLISH	DIM K METRIC	DIM L ENGLISH	DIM L METRIC	NOTES
95736-X02	1 X 2	0.400	10.16	0.100	2.54	—
95736-X03	1 X 3	0.500	12.70	0.200	5.08	—
95736-X04	1 X 4	0.600	15.24	0.300	7.62	—
95736-X05	1 X 5	0.700	17.78	0.400	10.16	—
95736-X06	1 X 6	0.800	20.32	0.500	12.70	—
95736-X07	1 X 7	0.900	22.86	0.600	15.24	—
95736-X08	1 X 8	1.000	25.40	0.700	17.78	—
95736-X09	1 X 9	1.100	27.94	0.800	20.32	—
95736-X10	1 X 10	1.200	30.48	0.900	22.86	—
95736-X11	1 X 11	1.300	33.02	1.000	25.40	—
95736-X12	1 X 12	1.400	35.56	1.100	27.94	—
95736-X13	1 X 13	1.500	38.10	1.200	30.48	—
95736-X14	1 X 14	1.600	40.64	1.300	33.02	—
95736-X15	1 X 15	1.700	43.18	1.400	35.56	—
95736-X16	1 X 16	1.800	45.72	1.500	38.10	—

DASH NO	OVERPLATING	UNDERPLATING
-1YY	30u"/.76u MIN (SEE NOTE 8)	50u"/1.27u MIN Ni
-1YYLF	30u"/.76u MIN (SEE NOTE 8)	50u"/1.27u MIN Ni
-4YY	100u"/2.54u MIN Sn (NOTE 9)	50u"/1.27u MIN Ni
-4YYLF		50u"/1.27u MIN Ni

PRODUCT NUMBER
95736-XYLF

— LEAD FREE OPTION
— NO. OF POSITIONS
— PIN PLATING (SEE TABLE)
— BASE PART NUMBER



SCALE 3/1
RECOMMENDED HOLE PATTERN

NOTE

- MOLDING MATERIAL: HIGH TEMPERATURE PLASTIC
FLAME RETARDANT PER UL-94V-0. COLOR: NATURAL
- PIN MATERIAL: 3/4 HD PHOS. BRONZE
- LOGO TO BE LOCATED APPROX. AS SHOWN.
- TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED,
BOTH ENDS.
- FOR LEAD FREE OPTION ADD "LF" IN THE END OF
THE EXISTING PART NUMBERS.
- IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 20-30 SECONDS IN A CONVECTION,
INFRA-RED OR VAPOR PHASE REFLOW OVEN. SEE APPLICATION
NOTES/PROCEDURES IF THEY ARE AVAILABLE
- OR THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK
TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION
NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT THE MANUFACTURER'S CHOICE
- "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND
HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL
INTERCONNECT ENVIRONMENTS."

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADER	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title CLINCHER™ LATCH HEADER RIGHT ANGLE	
H				angles	linear		scale 4:1 sheet 2 of 2 size A3	
				0°±2'	XXX±.006/XX±0.13		dwg no 95736	
				dr	T.BREWBAKER 5/23/95		type Product Customer Drawing	
				engr	T. HANNA 5/23/95			
				chr	T. HANNA 5/23/95			
				appd	T. HANNA 7/6/95			
sheet index	revision sheet							