

MODULAR JACKS AND PLUGS: GWX /GWX-SMT Series

Right Angle Modular Jack, Tab Up

Product Features:

Low Profile Design Suitable for PC Add-on
Tab up Design for Easy Insertion/Removal of Mating Plug
Available Fully Shielded for EMI/RFI Protection
Available with Through Hole or Surface Mount
Contact Options
CSA/NTRL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing

High Temperature Thermoplastic, UL 94V-0 Rated,
Black Color

Contact Material

Phosphor Bronze

Contact Plating

Standard: Nickel Underplating, Selectively Plated
Gold Flash

50 Option: Nickel Underplating, Selectively Plated
50µ" Gold

Contact Area, Gold Flash on Solder tails

Shield Material

Copper Alloy, Nickel Plated

Electrical Characteristic

Insulation Resistance

500 Megohms Min.

Rated Voltage

125V DC

Contact Resistance

20 milliohms Max.

Rated Current

1.5A

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-				
Series		Shield Option	No. of Positions & Contacts	Plating Options	Packaging Option

Series

GWX - Through Hole, Right Angle

GWX-SMT - Surface Mount, Right Angle

Shield Option

N - Non-Shielded

S - Fully Shielded

S3 - Fully Shielded with Tabs on Top (Available only with Through Hole)

S9 - Fully Shielded with Tabs on Top and Sides

Number of Positions/Contacts

88 - 8 Positions / 8 Contacts

Plating Option

Blank - Gold Flash

50 - 50µ" Gold Plating

Packaging Option


Blank - Tray

TR - Tape & Reel (Available only with SMT Option)

Contact Kycon for Other Options

GWX-S-88

Dimensions in mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[GWX-S3-88-50](#) [GWX-S9-88](#) [GWX-S9-88-50](#) [GWX-SMT-S9-88-50](#) [GWX-S-88-50](#) [GWX-S-88](#) [GWX-SMT-S9-88](#)
[GWX-N-88](#) [GWX-N-88-50](#) [GWX-S3-88](#) [GWX-SMT-N-88](#) [GWX-SMT-N-88-50](#) [GWX-SMT-N-88-50-TR](#) [GWX-SMT-N-](#)
[88-TR](#) [GWX-SMT-S-88](#) [GWX-SMT-S-88-50](#) [GWX-SMT-S-88-50-TR](#) [GWX-SMT-S-88-TR](#) [GWX-SMT-S9-88-50-TR](#)
[GWX-SMT-S9-88-TR](#)