

Zebra® G-Series™ printers



Making a difference to your desktop

Zebra's G-Series compact desktop printers deliver best-in-class speed and performance for print widths up to 104mm (4"). From the basic GK™ model to the feature-rich GX™ model, the G-Series printers offer a reliable, durable and flexible desktop solution for any printing application and budget.

Built with Zebra durability and reliability, the G-Series GK model provides the best value of all basic desktop thermal printers, while the premier GX model supports a variety of industries and applications with the widest range of features. Choose the space-saving direct-thermal version of either model for the smallest footprint of any 104mm (4") desktop printer, or the direct-thermal/thermal-transfer version to save users time with the easiest ribbon-loading system available.

With both EPL™ and ZPL® native on all models and a variety of connectivity options for personal, local and networked systems, the G-Series printers integrate easily and seamlessly with other Zebra printing solutions.

Zebra's G-Series printers support many applications, including:

Healthcare:

- Patient identification
- Sample and specimen identification
- Sterile services labelling
- Pharmacy prescription labelling

Retail:

- Product labelling
- Price mark-down
- Shelf-edge labelling
- Voucher and receipt printing

Travel:

- Boarding passes
- Bag tags

Hospitality, service & leisure:

- Event and exhibition ticketing
- Fast-food labelling
- Gaming and betting slips

Supply chain:

- Process, product and shipping labelling

Post & parcel:

- Electronic franking
- Address labelling

Specifications at a glance*

Standard features

- Print methods: Direct-thermal or thermal-transfer
- Programming languages: EPL and ZPL as standard
- Construction: Dual-wall frame
- Tool-less replacement of printhead and platen
- OpenACCESS™ for easy media loading
- Quick and easy ribbon loading
- Auto-calibration of media
- 32-bit RISC processor
- Odometer
- Unicode™

Printer specifications

Resolution

- 8 dots per mm/203dpi
- 12 dots per mm/300dpi (GX430t™)

Memory

- Standard: 4MB flash; 8MB SDRAM
- Optional: 64MB (68MB total) flash with real-time clock (GX models)

Print width

- 104mm/4.09"

Maximum print length

- 990mm/39.0"

Maximum print speed

- GK420: 127mm/5" per second
- GX420: 152mm/6" per second
- GX430: 102mm/4" per second

Media sensors

- Standard: Fixed reflective and transmissive sensors
- Adjustable reflective and multi-position transmissive sensor (GX models, optional)

Media characteristics

Maximum label and liner length

- Maximum non-continuous: 990mm/39"

Maximum label and liner width

- 19mm/0.75" to 108mm/4.25"

Maximum media roll size

- 127mm/5" O.D.

Media thickness

- 0.076mm/0.003" to 0.19mm/0.0075"

Media types

- Roll-fed or fanfold, die-cut or continuous direct-thermal labels with or without black mark, tag stock, continuous receipt paper, wristbands

Ribbon characteristics

Outside diameter

- 35mm/1.36"

Length

- 74m/244' (when using 0.08mm ribbon thickness)

Ratio

- 1:1 media roll to ribbon

Width

- 33.8mm/1.33" to 109.2mm/4.3"

Core inner diameter

- 12.7mm/0.5"

Operating characteristics

Environmental

- Operating temperature: 4.4°C to 41°C
- Storage temperature: -40°C to 60°C
- Operating humidity: 5% to 95% non-condensing
- Storage humidity: 5% to 95% non-condensing

Electrical

- Auto-detectable (PFC-compliant) 100–240VAC, 50–60Hz

Agency approvals

- Emissions: FCC Part 15, Subpart B, VCCI, C-Tick
- Emissions and Susceptibility: (CE): EN 55022 Class B, EN 61000-3-2, EN 61000-3-0 and EN 55024, CCC
- Safety: CB Scheme IEC 60950:1991 +A1 +A2 +A3 +A4, TÜV NRTL, IRAM NOM, AAMI, CCC

Physical characteristics

Width

- Direct-thermal: 171mm/6.75"
- Thermal-transfer: 193mm/7.6"

Height

- Direct-thermal: 152mm/6.0"
- Thermal-transfer: 190mm/7.5"

Depth

- Direct-thermal: 210mm/8.25"
- Thermal-transfer: 254mm/10.0"

Weight

- Direct-thermal: 1.4kg/3lb
- Thermal-transfer: 2.1kg/4.6lb

ZebraLink™ Solutions

Software (downloadable from www.zebra.com)

- ZebraDesigner Driver
- ZebraDesigner™ Pro
- ZebraDesigner
- ZebraNet™ Bridge Enterprise
- ZebraNet Utilities v7.0
- Zebra Setup Utilities
- POS Driver

Networking/Connectivity

- ZebraNet® 10/100 Print Server (optional)
- 802.11g wireless LAN (optional)
- Bluetooth® wireless PAN (optional)

Firmware

- EPL2™
- EPL Line Mode (direct-thermal only – GK420D and GX420D)
- ZPL II®
- XML-enabled printing
- ZBI 2.0™
- Web View
- Alert

Communication and interface capabilities

- Auto-sensing RS-232 serial interface, DB-9
- USB 1.1, bi-directional
- Parallel (Centronics®), bi-directional
- ZebraNet 10/100 Print Server (optional)
- 802.11g wireless (GX models, optional)
- Bluetooth wireless (GX models, optional)
- Wireless options include LCD for visual communication

Fonts/Graphics/Symbologies

Fonts and character sets

- 16 resident expandable ZPL II bitmap fonts
- One resident scalable ZPL font
- Five resident expandable EPL2 fonts
- Native OpenType™ font support
- Unicode-compliant for multi-language applications

Graphics features

- Supports user-defined fonts and graphics including custom logos
- ZPL II drawing commands for boxes and lines

Barcode symbologies

- Barcode ratios: 2:1 (non-rotated) and 3:1 *For EPL and ZPL except where noted*
- Linear Barcodes: Codabar, Code 11 (ZPL), Code 39, Code 93, Code 128, EAN-8, EAN-13, EAN-14 (ZPL), German Post Code (EPL), GS1 DataBar (RSS), Industrial 2-of-5 (ZPL), Interleaved 2-of-5, ISBT-128 (ZPL), Japanese Postnet (EPL), Logmars (ZPL), MSI, Plessey, Postnet, Standard 2-of-5 (ZPL), UCC/EAN-128 (EPL), UPC-A, UPC-A and UPC-E with EAN 2 or 5 digit extensions, UPC-E, UPC and EAN 2 or 5 digit extensions (ZPL)
- Two-dimensional: Codablock (ZPL), Code 49 (ZPL), Data Matrix, (ZPL), MaxiCode, MicroPDF417, PDF417, QR Code

Options and accessories

- Label dispenser with label-present sensor
- ZebraNet 10/100 Print Server – internal and external Ethernet options for network communication and printing
- 802.11g wireless (GX models)
- Bluetooth wireless (GX models)
- Wireless options include LCD for visual communication
- Adjustable media sensor (GX models)
- Cutter for various media types (GX models)
- 300dpi print resolution printing for fine detail and crisp images (GX430t)
- 64MB flash memory with real-time clock for total of 68MB (GX models)
- Font packs – Asian and other international font kits
- KDU Plus™ and KDU™ keyboard display units for standalone printing solutions
- Interface cables and adaptors
- Heavy-duty keyed locking mechanism secures the media chamber and reinforced media viewing window (GX420s™ model only)



*Specifications subject to change without notice.

©2012 ZIH Corp. EPL, EPL2, KDU, KDU Plus, OpenACCESS, ZBI 2.0, ZebraDesigner, ZebraLink, ZebraNet and all product names and numbers are Zebra trademarks, and Zebra, representation of Zebra Head, ZebraNet, ZPL and ZPL II are registered trademarks of ZIH Corp. All rights reserved. Bluetooth is a registered trademark of the Bluetooth SIG, Inc. OpenType is either a registered trademark or a trademark of Microsoft Corporation in the United States and/or other countries. Unicode is a trademark of Unicode, Inc. Centronics is a registered trademark of Centronics Data Computer Corporation. All other trademarks are the property of their respective owners.



SEE MORE.
DO MORE.

www.zebra.com



Please recycle after use

12574L Rev.4 (02/12)