



TR30R SERIES

30W SWITCHING

ADAPTER



* Not CE certified for the EU"

Features

- * Universal Input: 90-264VAC
- * Interchangeable AC Plugs
- * Meets EN61204-3 Class B and CISPR/FCC Class B
- * High Efficiency to 83% Typical
- * Continuous Short Circuit Protection
- * Over Voltage Protection
- * Provide PSE Mark (Option)

Ordering information

TR30RXXX-	XX	E	X	-	XX	-	BK
Model No.	DC Plug Type		DC Cable Length and Type		Color of Overmold Case		
	*Please see Page213 for more detailed descriptions		01: 720mm		BE: Blue		
			02: 1200mm		GY: Gray		
			03: 1800mm		RD: Red		
			11: 720mm with Ferrite Core		PE: Purple		
			12:1200mm with Ferrite Core		OR: Orange		
			13:1800mm with Ferrite Core				
			*18AWG/UL1185				

MODEL	OUTPUT VOLTAGE	MAX. LOAD	MIN. LOAD	RIPPLE& NOISE	VOLTAGE ACCURACY	LINE REGULATION	LOAD REGULATION	%EFF.
TR30R050	5V	5.0A	0A	1%	±4%	±1%	±6%	68% Typ.
TR30R090	9.0V	3.3A	0A	1%	±2%	±1%	±3%	77% Typ.
TR30R0120	12V	2.5A	0A	1%	±2%	±1%	±2%	78% Typ.
TR30R0150	15V	2.0A	0A	1%	±2%	±1%	±2%	80% Typ.
TR30R0180	18V	1.65A	0A	1%	±2%	±1%	±2%	80% Typ.
TR30R0240	24V	1.25A	0A	1%	±2%	±1%	±2%	83% Typ.



Specifications

INPUT SPECIFICATIONS:

Voltage 90~264Vac
 Frequency 47 to 63Hz
 Input Current 100Vac/0.8A max., 240Vac/0.5A max.
 Inrush Current 50A max. @240Vac
 Leakage Current 0.25mA max.

OUTPUT SPECIFICATIONS:

Holdup Time 10ms typ. @115Vac
 Short Circuit Protection Hiccup Mode Continuous(Auto Recovery)
 Over Voltage Protection TVS Component to Clamp

GENERAL SPECIFICATIONS:


Isolation Input to output = 4,242VDC
 Operating Temperature 0 ~ 60°C (see Drating Curve)
 Storage Temperature -20~85°C
 Humidity 93% RH max. Non condensing
 Cooling Natural Convection
 Switching Frequency 60KHz Typical
 MTBF MIL-HDBK-217F, GB, 25°C /115VAC 200K hrs min.
 Altitude 2000m
 Dimensions 4.234x2.267x1.319Inches (107.77x57.60x33.50mm)
 Weight 300g(0.66 Pounds)

SAFETY AND EMC:

Emission and Immunity EN61204-3, EN61000-3-2, EN61000-3-3
 FCC CFR Title 47 Part 15 Subpart B
 Safety IEC60950-1, UL60950-1, EN60950-1


Mechanical Specification

All Dimensions are in inches(mm)
 Tolerance: Inches: X.XXX±0.02
 Millimeters: X.XX±0.5



Typical at 25°C, nominal line and 75% load, unless otherwise Specified

TR30R Series Derating Curve



NOTE:

1. Voltage setpoint at 60% load
2. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for Ripple & Noise measuring @20MHz BW.
3. Line regulation measured from 100Vac to 240Vac, full load.
4. Load regulation measured from 60% to full load and from 60% to 20% load (60% +/- 40% load)
5. "Various TR Series adapters are PSE certified. PSE certification alone is not sufficient for importation into Japan. A valid PSE mark must contain the name of the importer as shown in the example below. If PSE mark is required, the name of the registered importer must be supplied to Cincon on order placement. Product labels will not contain PSE mark if importer name is not supplied. Consult factory or local representative for details"



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[TR30R120-11E03-GY-BK](#) [TR30R050-12E03-GY-BK](#) [TR30R090-12E03-GY-BK](#) [TR30R150-11A03-GY-BK](#)
[TR30R050-11A03-GY-BK\(ROHS\)](#) [TR30R150-12E03-GY-BK](#) [TR30R240-12E03-GY-BK](#) [TR30R090-11A03-GY-BK](#)
[TR30R050-11E03-GY-BK](#) [TR30R180-11E03-GY-BK](#) [TR30R180-12A03-GY-BK](#) [TR30R240-11E03-BE-BK W/4 PLUG](#)
[KIT](#) [TR30R240-11E03-GY-BK](#) [TR30R120-12E03-GY-BK](#)