


1550 & 1350 Hi-Inrush Switches 150A to IEC65 and 16A 250Vac



1550 Series

16(4)A 250Vac T125

UL CSA 16A 250Vac

UL CSA (2 position) 250Vac 1hp, 125Vac ½hp

UL CSA (3 position) 250Vac ½hp, 125Vac ¼hp

Inrush 36A to EN61058-1 & 20A 28Vdc (In house tests)

1350 Hi Inrush Series

© 150A Inrush to IEC 65

16(4)A 250Vac T85 1E4 (10,000 Operations)

UL CSA 20A 250Vac


UL CSA 250Vac 1hp, 125Vac ½hp

UL 85 C, file E45221

CSA file LR10990


20A 28Vdc (In house test)

3mm contact gap except where marked µ.




TERMINAL CODE


C




H




K



T



X



SWITCH FUNCTION CODE

Approvals & ratings vary with function
On Off Switches are On when pressed over terminal 1

Standard
1550 ♦

High inrush
1350 ♦

ON - OFF

16(6)A T125 5E4 available on request

ON - OFF
(momentary ON)

ON - OFF
(momentary OFF)

ON - OFF
Lit

ON - ON

ON - ON
(momentary 1 side)





ON - OFF - ON

ON - OFF - ON
(momentary 1 side)

ON - OFF - ON
(momentary 2 sides)


OFF - A - A+B
Selective
other circuits available

Indicator




ROCKER CODE


A Softline




V Curved




N Slimline sub-panel rocker




P Lit window




X Softline 2 Colour Rocker



A Softline




Most switches shown can be supplied with single pole switching in double pole bodies



BODY CODE

	Panel cut-outs*	Flanges
A	Gloss or Matt	
B	Matt only	
L	Matt only	
Q	Gloss or Matt	
R	Matt only	
T	Matt only	

DIMENSIONS



Panel thickness

A,Q	0.75 to 3.3mm
L,B,T	0.75 to 2.5mm
R	0.75 to 3.0mm

Moisture resistant switches

Certain switches can be assembled with an internal barrier for improved resistance to the ingress of water or dust. Applications should be discussed with the factory.

Moisture resistant covers (IP65)

Snap on to A, L, Q or T bodies (add G after body code). A panel sealing washer W42 is also available for certain body sizes. Covers or washers reduce panel thickness range & are not suitable for momentary types.

*** Momentary Switches Panel cut-outs**

Contact our Sales department for advice on cut-out sizes.

Examples of printing

