




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		B1	REVISED PER ECO-11-004820	11MAR11	RK	HMR


- 1 WIRE RANGE: 0.2–0.8mm² (24–18 AWG).
- 2 INSULATION RANGE: 1.5–2.4 DIA.
- 3

FINISH: 0.76μm MIN GOLD OVER 1.27μm MIN NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 4


FINISH: 2.54μm MIN TIN ON ALL SURFACES IN THIS AREA.



SECTION A-A



SECTION B-B



SECTION C-C

GOLD 34	PHOS. BRZ.	1586315-4
PRE-TIN	PHOS. BRZ.	1586315-3
GOLD 34	BRASS	1586315-2
PRE-TIN	BRASS	1586315-1
FINISH:	MATERIAL:	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 14-OCT-2003		 TE Connectivity			
		CHK D. COLEY 14-OCT-2003					
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD D. COLEY 14-OCT-2003		NAME	
		0 PLC ±		TERMINAL LOOSE PIECE, SOCKET VAL-U-LOK(TM)			
		1 PLC ± 0.3 [.01]					
		2 PLC ± 0.15 [.004]					
		3 PLC ± 0.050 [.0020]		PRODUCT SPEC			
		4 PLC ±					
		ANGLES ±		APPLICATION SPEC			
MATERIAL		FINISH		SIZE		CAGE CODE	
				DRAWING NO		RESTRICTED TO	
				A2 00779		C=1586315	
						—	
CUSTOMER DRAWING				SCALE		SHEET	
				10:1		1 of 1	
						REV	
						B1	