

End Brushes Record and Alpha

Record: Record end brushes are produced from crimped wire in various qualities. They are the perfect brush for hard-to-reach areas such as corners, drilled holes and recesses of all kinds.


Fill types: RECORD

STD – Steel wire, natural hard, crimped.

INOX – Stainless steel wire, acid resistant, crimped.

MES – Brass wire (Cu-Zn), crimped.

Applications: Removal of paint, rust and primer, and the cleaning of moulds and castings.



Alpha: Heat-resistant polyamide filaments, impregnated, with 20–40 % abrasive grit.

Fill type: ALPHA

ANS – ANDERLON abrasive filaments, silicon-carbide grit, crimped.

Applications: The removal of fine burrs and the production of matt and satin finishes.



End Brushes Record



Wear eye protection!

Pinselbürsten Record

Dimensions/ Abmessungen Ø	d1	L	D	L1	RPM/ UPM	Type	0.20 INOX	0.30 INOX	0.20 MES	0.30 MES
mm	mm	mm	mm	mm	max.		Art.-No.	Art.-No.	Art.-No.	Art.-No.
Record										
12 (1/2")	10	20	6	60	20000	P 10	9310.4300	9310.4500	9310.6300	9310.6500
17 (11/16")	15	22	6	65	18000	P 15	9315.4300	9315.4500	9315.6300	9315.6500
24 (15/16")	22	25	6	68	18000	P 22	9322.4300	9322.4500	9322.6300	9322.6500
30 (1 1/4")	28	25	6	68	15000	P 28	9328.4300	9328.4500	9328.6300	9328.6500
10 (3/8")	8	20	6	120	20000	P 8 L-95	9308.4310	9308.4510	9308.6310	9308.6510
12 (1/2")	10	20	6	120	20000	P 10 L-100	9310.4310	9310.4510	9310.6310	9310.6510
18 (11/16")	16	22	6	147	18000	P 16 L-125	9316.4310	9316.4510	9316.6310	9316.6510
50 (2")	22	25	6	68	15000	G 2250	9322.4301	9322.4501	9322.6301	9322.6501
	28	20	6	63	15000	G 2850	9328.4303	9328.4503	9328.6303	9328.6503
70 (2 3/4")	28	25	6	68	15000	G 2870	9328.4301	9328.4501	9328.6301	9328.6501

End Brushes Record



Wear eye protection!

Pinselbürsten Record

Dimensions/ Abmessungen Ø	d1	L	D	L1	RPM/ UPM	Type	0.20 STD	0.30 STD	0.50 STD
mm	mm	mm	mm	mm	max.		Art.-No.	Art.-No.	Art.-No.
Record									
12 (1/2")	10	20	6	60	20000	P 10	9310.0300	9310.0500	9310.0800
17 (11/16")	15	22	6	65	18000	P 15	9315.0300	9315.0500	9315.0800
24 (15/16")	22	25	6	68	18000	P 22	9322.0300	9322.0500	9322.0800
30 (1 1/4")	28	25	6	68	15000	P 28	9328.0300	9328.0500	9328.0800
10 (3/8")	8	20	6	120	20000	P 8 L-95	9308.0310	9308.0510	9308.0810
12 (1/2")	10	20	6	120	20000	P 10 L-100	9310.0310	9310.0510	9310.0810
18 (11/16")	16	22	6	147	18000	P 16 L-125	9316.0310	9316.0510	9316.0810
50 (2")	22	25	6	68	15000	G 2250	9322.0301	9322.0501	9322.0801
	28	20	6	63	15000	G 2850	9328.0303	9328.0503	9328.0803
70 (2 3/4")	28	25	6	68	15000	G 2870	9328.0301	9328.0501	9328.0801