

Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Audio Wire and Cable

Electrolytic Tough Pitch (ETP) High-Conductivity Copper Speaker Cables
Parallel Zip Constructions

Jameco Part Number 232629
(9718-368-100)




Description	Part No.	UL NEC/ C(UL) CEC Type	No. of Cond.	Standard Lengths		Standard Unit Weight		Insulation Thickness		Nominal OD	
				ft.	m	Lbs.	kg	Inch	mm	Inch	mm

24 AWG Stranded (7x32) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • PVC Jacket (Available in Clear, White, Brown or Chrome)

300V 60°C (Clear)	8782		2	U-1000 ▲	U-304.8	6.0	2.7	.017	.43	.058	1.47
300V 75°C (Chrome, Brown, White)				1000 •	304.8	7.0	3.2			x	x
										.116	2.95




▲U-1000 ft. put-up available in Brown or Chrome only.

•1000 ft. put-up available in White or Clear only.

22 AWG Stranded (7x30) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • Clear PVC Jacket


300V 60°C	9712		2	1000	304.8	9.0	4.1	.017	.43	.065	1.65
										x	x
										.130	3.30



20 AWG Stranded (7x28) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • Clear or Chrome PVC Jacket


300V 60°C	8649		2	1000	304.8	12.0	5.5	.018	.46	.073	1.85
VW-1										x	x
										.146	3.71



18 AWG Stranded (16x30) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • Clear PVC Jacket


300V 60°C	9708		2	100	30.4	2.8	1.3	.032	.81	.110	2.79
				U-500	U-152.4	10.5	4.8			x	x
				500	152.4	10.5	4.8			.220	5.59
				U-1000	U-304.8	20.0	9.1				
				1000	304.8	21.0	9.5				



16 AWG Stranded (26x30) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • Clear PVC Jacket


300V 60°C	9716		2	U-1000	U-304.8	8.0	3.6	.027	.69	.115	2.92
				1000	304.8	7.0	3.2			x	x
										.230	5.84



14 AWG Stranded (19x27) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • Clear PVC Jacket

60°C	9717		2	U-1000	U-304.8	43.0	19.5	.035	.89	.146	3.71
				1000	304.8	42.0	19.1			x	x
										.292	7.42



12 AWG Stranded (65x30) ETP High-conductivity Copper • Parallel: (1) Tinned, (1) Bare

PVC Insulation • Clear PVC Jacket

60°C	9718		2	500	152.4	33.0	15.0	.045	1.14	.185	4.70
				1000	304.8	66.0	30.0			x	x
										.370	9.40

