





Tous droits réservés. Reproduction ou utilisation sans autorisation de FCI S.A. est formellement interdite.

All rights reserved. Reproduction or use without written authority from FCI S.A. is strictly prohibited.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL

PRODUCT NR.	DIM "A"
85856-X01/X01LF	5.00 REF.
85856-X11/X11LF	3.35 REF.



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

- NOTES:
1. BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 2. TERMINAL MATERIAL: PHOSPHOR BRONZE.
 3. PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 , OR 2-8 μ m PURE Sn FOR P/N WITH LF SUFFIX.
 4. LOAD IN THIS DIRECTION (E.G. THROUGH CODING) 30 NEWTON MAXIMUM PER CONNECTOR.
 5. LOAD IN THIS DIRECTION 15 NEWTON MAXIMUM PER CONNECTOR.
 6. TO ENSURE PROPER ALIGNMENT OF MULTIPLE MODULES ON A BOARD THE USE OF A FIXTURE IS RECOMMENDED.
 7. PRODUCT MARKING: PARTNUMBER & BATCH I.D.
 8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008 .
 9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI ELECTRONICS	
ltr	ecr no	dr	date	linear		projection		title	www.fciconnect.com
A	H40453	DDb	940712					STR FEMALE STB	
B	0005-0061	CLu	050328					SIGNAL 12MM	
C	0007-0169	Cent	05/15/07	angles				product family	NETRAL (tm)
D	0008-0171	TER	8/26/08	dr	D. de Bil	940712	mm	size dwg no	213
E	0009-0068	Cent	06/06/08	engr	E. Feijen	940712	scale	A2	85856
				chr	E. Feijen	940712	5:1	sheet	1 of 1
				app	E. Feijen	940712			
sheet index	revision	sheet	E	1					