



2.75W Compact Fixed Blade Charger Small/Thin Wall Plug Adapter with DC Cord



Features

- North America Fixed Blade AC Input
- CC & CV control
- Ecodesign ErP Directive 2009/125/EC level 2 annex 1b compliant
- Limited Power Source
- Class B EMI
- No Y Caps
- Class 2 Output

Applications

- MPEG Players
- PDAs
- Medical Test Device Charging
- Personal Electronics
- Digital Cameras
- Cordless Tools

Safety Approvals

- cUL/UL

Mechanical Characteristics

- Length: 39.4mm (1.65in)
- Width: 43mm (1.65in)
- Height: 21.0mm (0.87in)
- Weight: 45g (1.59oz)

Output Specifications

Model	DC Output Voltage	Load		Ripple P-P (max)	Regulation	
		Min.	Max.		Line	Load
PSM03A-050-R	5V	0A	0.55A	100mV	±5%	
PSM03A-075-R	7.5V	0A	0.366A	100mV	±5%	
PSM03A-090-R	9V	0A	0.305A	100mV	±5%	
PSM03A-100-R	10V	0A	0.275A	120mV	±5%	
PSM03A-120-R	12V	0A	0.23A	200mV	±5%	

PhiHong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

100 to 240VAC

90 to 264VAC

100mA (RMS) max.

0.25mA maximum

(Cold start @ ambient 25°C)

<0.15W max. @ 230VAC at no load

2.75W Maximum

Meets Level V Efficiency Requirements

0.03W maximum at 115VAC/230VAC

10mS min. @ 120VAC and max. load

The output is equipped with over-voltage and short-circuit protection. The output can be shorted permanently without damage.

Non-operation	-25 to +75°C
---------------	--------------

Operation	20 to 90%
-----------	-----------

Flicker: EN61000-3-3

EN55022 Class B

Primary to Secondary: 3000VAC, 10mA for 60s

Primary to Secondary: >100M ohm 500VDC

1500mm

5.5mm x 2.1mm x 9.5 center positive barrel

Technical drawings of the Laser Engraving Kit components. The top row shows a perspective view of the laser unit, a top-down view of the cable with a total length of 1500 ± 50 , and a side view of the cable with a diameter of 21. The bottom row shows a front view of the laser unit with a width of 43 and a height of 56.4, and a side view of the cable with a width of 39.4. The cable is labeled "LASER ENGRAVING" and "TIE".