




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
H	—	D		REVISED PER ECR ECR-11-009918	14MAY11	RC
		E		ECO-11-024491	13DEC11	SY

13	OBSOLETE	6			1-5352457-9
		5			5352457-9
13	OBSOLETE	4			5352457-4
		3			5352457-1
		FINISH		MATERIAL	PARTNUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25AUG2004	TE Connectivity	
		CHK	27OCT2004		
		APVD	27OCT2004	NAME	
		PRODUCT SPEC			
		APPLICATION SPEC	108-19082	Z-PACK 2mm HM TYPE A 110 POS. VERTICAL FEMALE CONNECTOR WITH LOCATION PEG	
		WEIGHT	114-19029		
		CUSTOMER DRAWING		SIZE	RESTRICTED TO
				A2	—
				CAGE CODE	
				DRAWING NO	
				00779	
				SCALE	
				5:1	
				SHEET	
				1 of 1	
				REV	
				E	

NOTES:

- ⚠ MATERIAL CONTACT; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER
UL-RATING 94V0 (GRAY).
- ⚠ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
- ⚠ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
- ⚠ CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
- ⚠ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (110 HOLES).
- ⚠ HOLES IN ROW f AND z FOR POSSIBLE FUTURE USE OF
GROUND RETURN SHIELD. (SHIELDS NOT YET TOOLED)
- ⚠ LOCATION PEG.
- ⚠ AREA RESERVED FOR KEYING PART (BASIC P.N.:100526).
- ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

