

ECP 3-6

Order No.: 0916536



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=0916536>

Selective circuit breaker, can be plugged in TMCP socket, signaling by two-color LED, floating signal contact, on/off pushbutton, width: 12.5 mm, color: black

Commercial data

GTIN (EAN)	4017918927226
sales group	A043
Pack	5 pcs.
Customs tariff	85362010
Weight/Piece	0.0704 KG
Catalog page information	Page 467 (CL-2009)

Product notes

WEEE/RoHS-compliant since:
03/10/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Color	black
Insulating material	PA-F
Inflammability class acc. to UL 94	V0

Dimensions

Width	12.5 mm
Length	60 mm
Height NS 35/7,5	144 mm
Height NS 35/15	151.5 mm

Technical data

Fuse type	Automatic device
Nominal current I _N	6 A
Nominal voltage U _N	24 V DC (up to max. 32 V)
Switching capacity I _{CN}	(Active current limitation)

Certificates / Approvals



Certification


UL, VDE-PZI

Additional products


Item	Designation	Description
Assembly		
0916592	TMCP CONNECT LR	Fuse modular terminal block, Length: 115 mm, Width: 6 mm, Color: black
0916589	TMCP SOCKET M	Modular socket element, 2-position, for holding two circuit breakers, each with a single position

Diagrams/Drawings


Block diagram



Diagram




Functional drawing



- 1 = Selective circuit breaker
- 2 = Socket termination element
- 3 = Modular socket element
- 4 = Socket termination element

Circuit diagram



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;