

FEATURES


- **Standard 6.0mm x 3.5mm Ceramic Surface Mount Package**
- **Fundamental Crystal Design**
- Frequency Range 8 – 50 MHz
- Frequency Tolerance, ± 30 ppm Standard
[other tolerances available]
- Frequency Stability, ± 50 ppm Standard
[other stabilities available]
- Operating Temperature to -40°C to $+85^{\circ}\text{C}$
- Stable Frequency Over Temperature and Drive Level
- Tape & Reel Packaging Standard, EIA-481
- **RoHS/Green Compliant (6/6)**



APPLICATIONS

The Model 406 is a seam sealed ceramic packaged crystal offering reduced size, ideal for high-density circuit board applications. M406 offers reliable precision and excellent shock performance suitable for wireless communications, broadband access, WLAN/WiMax/WIFI, portable equipment, test and measurement, PCMCIA, computers and modems.

ORDERING INFORMATION



1] Only available with temperature range code "C".


2] Frequency is recorded with two leading digits before the 'M' and 5 significant digits after the 'M' (including zeros).

[Ex. XXMXXXX (16M38400), XXMXXXX (14M31818)]

**Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.**

PACKAGING INFORMATION [reference]

Device quantity is 1k pcs. maximum per 180mm reel.



ELECTRICAL CHARACTERISTICS


ELECTRICAL PARAMETERS	PARAMETER	VALUE
	Frequency Range	8.0 MHz to 50.0 MHz
	Operating Mode	Fundamental
	Crystal Cut	AT-Cut
	Frequency Tolerance @ 25°C	± 30 ppm standard [± 10 ppm, ± 15 ppm and ± 20 ppm Available]
	Frequency Stability Tolerance [Operating Temperature Range, Referenced to 25°C Reading]	± 50 ppm standard [± 10 ppm, ± 15 ppm, ± 20 ppm, ± 30 ppm and ± 40 ppm Available]
	Operating Temperature Range	-20°C to +70°C -40°C to +85°C
	Equivalent Series Resistance	See ESR Table
	Load Capacitance or Resonance Mode	See Ordering Information
	Shunt Capacitance (C_0)	4.0 pF typical 7.0 pF maximum
	Drive Level	10 µW typical 100 µW maximum
	Aging @ +25°C	±3 ppm/yr typical ±5 ppm/yr maximum
	Insulation Resistance	500M Ohms @ 100V _{DC} ±15V _{DC}
	Storage Temperature Range	-55°C to +125°C
	Reflow Condition, per JEDEC J-STD-020	+260°C maximum, 10 Seconds maximum

EQUIVALENT SERIES RESISTANCE TABLE

FREQUENCY RANGE	MODE of OSCILLATION	ESR Maximum
8.00 MHz - 9.999 MHz	Fundamental	80 Ohms
10.00 MHz - 15.999 MHz	Fundamental	60 Ohms
16.000 MHz - 50.000 MHz	Fundamental	40 Ohms

MECHANICAL SPECIFICATIONS

PACKAGE DRAWING




MARKING INFORMATION

1. XX.XXX – Frequency marked with 3 significant digits after the decimal.
2. C – CTS identifier.
3. ** – Manufacturing Site code.
4. YWW – Date Code, Y – Last Digit of Year, WW – Week.

NOTES

1. Complete CTS part number, frequency value and date code information must appear on reel and carton labels.
2. Termination pads (e4); barrier plating is nickel (Ni) with gold (Au) flash plate.
3. Terminations #2, #4 and metal lid are connected internally and may be connected to ground for EMI suppression.
4. MSL = 1.

SUGGESTED SOLDER PAD GEOMETRY



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

406C35B10M00000	406C35B10M24500	406C35B12M28800	406C35B12M68800	406C35B13M00000
406C35B13M22500	406C35B14M00000	406C35B14M31818	406C35B14M85000	406C35B18M43200
406C35B19M44000	406C35B20M48000	406C35B22M00000	406C35B24M57600	406C35B27M00000
406C35B30M00000	406C35B32M76800	406C35B35M32800	406C35B38M88000	406C35B44M54500
406C35B48M00000	406C35B12M00000	406C35B16M00000	406I35D25M00000	406I35D27M00000
406I35E10M00000	406I35B19M44000	406I35D32M00000	406I35D24M00000	406C35D30M00000
406C35D14M31818	406C35D14M74560	406I35D12M00000	406I35D10M00000	406C35D25M00000
406C35D11M05920	406C35D16M93440	406C35D19M66080	406C35D24M57600	406C35D27M00000
406C35D32M00000	406C35D32M76800	406C35D40M00000	406C35D48M00000	406C35D50M00000
406C35D64M00000	406C35E08M00000	406C35E10M00000	406C35E11M05920	406C35E12M00000
406C35E14M31818	406C35E14M74560	406C35E16M00000	406C35E16M93440	406C35E19M66080
406C35E20M00000	406C35E24M00000	406C35E24M57600	406C35E25M00000	406C35E27M00000
406C35E32M00000	406C35E32M76800	406C35E40M00000	406C35E48M00000	406C35E50M00000
406C35E64M00000	406C35S14M31818	406C35S16M00000	406C35S18M43200	406C35S19M66080
406C35S20M00000	406C35S24M00000	406I35B10M00000	406I35B10M24500	406I35B12M28800
406I35B12M68800	406I35B13M00000	406I35B13M25500	406I35B14M00000	406I35B14M31818
406I35B14M85000	406I35B16M36800	406I35B18M43200	406I35B20M48000	406I35B22M00000
406I35B24M57600	406I35B27M00000	406I35B30M00000	406I35B32M76800	406I35B35M32800
406I35B38M88000	406I35B44M54500	406I35B48M00000	406I35D08M00000	406I35D11M05920
406I35D14M31818	406I35D14M74560	406I35D16M00000	406I35D16M93440	406I35D19M66080