

THRESHOLD DETECTOR *TMJ9902*

Packages; TO-8 (5 Pin), Surface Mount
and SMA Connectorized Housings

Features

- External Threshold Control - Voltage or Resistance
- -10 dBm to +10 dBm Input Operating Range
- Wide Operating Frequency 10 - 2000 MHz
- Environmental Screening Available


Specifications

CHARACTERISTIC	TYPICAL Ta= 25 °C	MIN/MAX Ta = -55 °C to +85 °C
Input Flatness (dB) P = -10 to +10dBm	+/- 0.4	+/- 1.0 Max.
Input VSWR (Max)	1.75:1	2.0:1
Threshold Control Level (V/Ohms) @ P _{IN} = -10 dBm @ P _{IN} = 0 dBm @ P _{IN} = +10 dBm	0.1/325 0.3/950 1.0/3400	- - -
Threshold Temp. Stability (dB) @ P _{IN} = -10 dBm @ P _{IN} = 0 dBm @ P _{IN} = +10 dBm	- - -	+/- 1.5 Max. +/- 1.0 Max. +/- 0.5 Max.
Threshold Hysteresis Voltage Control (dB) Resistance Control (dB)	<0.1 <1.0	- -
Output @ P _{IN} = Threshold (V)	3.2	2.7 Min.
Output Short Circuit Current (mA)	8	3.0 Min.
Rise Time/Fall Time (ns)	100	125 Max.
Power Vdc mA	+15 12	+15 15 Max.

Note: Care should always be taken to effectively ground the case of each unit.


Maximum Ratings

Operating Case Temperature..... - 55 °C to + 125 °C
Storage Temperature..... -62 °C to + 150 °C
Continuous RF Input Power.....+ 15 dBm
DC Voltage.....+ 17 Volts




Typical Performance Data


Control Voltage & Resistance vs. Input Power




Input VSWR




Input Power Flatness




Hysteresis (dB)



Input Power Flatness (dBm)



Input Power Flatness (dBm)



Amplifonix

2707 Black Lake Place, Philadelphia, PA 19154

TEL 215-464-4000 • • • • FAX 215-464-4001

9/14/03