Vertical Cavity Surface Emitting Laser in TO-46 Package

OPV302



Features:

- 850nm VCSEL technology
- High thermal stability
- Low drive current
- High output power
- Narrow beam angle




Description:

The OPV302 is a Vertical Cavity Surface Emitting Laser (VCSEL) packaged in a dome lens TO-46 package. VCSELs offer many advantages in sensing applications when compared to infrared LEDs. These devices require substantially lower drive currents to obtain the same amount of output power as LEDs. This feature allows VCSELs to be used in low power consumption applications such as battery operated equipment. The dome lens packaging creates a narrow beam angle from the device. Long distance applications may benefit from this feature as secondary optics may be eliminated, reducing total system cost. The OPV302 is optically and spectrally compatible with Optek's standard detector products such as the OP800 series phototransistors, OP830 series photodarlingtons and the OP910 photodiode.

Applications:

- Non-contact position sensing
- Photoelectric sensors
- **Optical** encoders
- Light curtains


OPV302				
Pin Connection				
1	VCSEL Anode			
2	VCSEL Cathode			
3	No Connection			





Additional laser safety information can be found on the Optek website. See application bulletin #221.

Classification is not marked on the device due to space limitations. See package outline for centerline of optical radiance. Operating devices beyond maximum rating may result in hazardous radiation exposure.





TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

.209

RoHS

Vertical Cavity Surface Emitting Laser in TO-46 Package





Electrical Specifications

Absolute Maximum Ratings (T _A = 25° C unless otherwise noted)				
Storage temperature range	-40° to +100°C			
Operating temperature range	0° to +85°C			
Lead soldering temperature [1/16 inch (1.6mm) from case for 5 sec with soldering iron]	260°C			
Maximum forward peak current, continuous	12 mA			
Maximum reverse voltage	5 V			
Maximum forward current, pulsed (1 μs P.W., 10% D.C.)	48 mA			

Electrical	Electrical Characteristics (T _A = 25° C unless otherwise noted)								
SYMBOL	PARAMETER	MIN	ТҮР	MAX	UNITS	TEST CONDITIONS			
P _{OT}	Total power out	1.5			mW	I _F = 7 mA			
I _{TH}	Threshold current			3.0	mA	Note 2			
V_{F}	Forward voltage			2.2	V	I _F = 7 mA			
I _R	Reverse current			100	nA	V _R = 5 V			
Rs	Series resistance	20		55	Ohms	Note 3			
η	Slope efficiency	0.28			mW/mA	Note 4			
λ	Wavelength	840		860	Nm				
Δλ	Optical bandwidth			0.85	Nm				
θ	Beam divergence		4		Degrees	FWHM			
Δη/ΔΤ	Temp coefficient of slope efficiency		-0.50		%/°C	(0° - 70°C), Note 4			
Δλ/ΔΤ	Temp coefficient of wavelength		0.06		Nm/°C	(0° - 70°C),			
ΔI _{TH}	Temp variance of threshold current		±1.0		mA	(0° - 70°C), Note 2			
$\Delta V_F/\Delta T$	Temp coefficient for forward voltage		-2.5		mV/°C	(0° - 70°C)			

NOTES:

- (1) RMA flux is recommended. Solder dwell time can be increased to 10 seconds when flow soldering.
- (2) Threshold Current is based on the two line intersection method specified in Telcordia GR-468-Core. Line 1 from 4 mA to 6 mA. Line 2 from 0 mA to 0.5 mA.
- (3) Series Resistance is the slope of the Voltage-Current line from 5 to 8 mA.
- (4) Slope efficiency, is the slope of the best fit LI line from 5 mA to 8 mA with 0.25mA test intervals.

Vertical Cavity Surface Emitting Laser in TO-46 Package

OPV302



